


Product data sheet

Characteristics

LA4DE2E

TeSys D - suppressor module - varistor - 24...48 V AC



Main

| | |
|---------------------------|--|
| Range | TeSys |
| Device short name | LA4D |
| Product or component type | Suppressor module |
| Product compatibility | 4P LC1D40008...D80008 3P LC1D80...D95 4P LC1D80004 |

Complementary

| | |
|------------------------------|--------------------------|
| Mounting location | Top |
| Mounting mode | By screws |
| Suppressor technology | Varistor (peak limiting) |
| [Uc] control circuit voltage | 24...48 V AC 50/60 Hz |
| Maximum peak voltage | 2 Uc |
| Product weight | 0.018 kg |

Environment

| | |
|---------------------------------------|-------------|
| Ambient air temperature for operation | -25...55 °C |
| Ambient air temperature for storage | -40...80 °C |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 14 g |
| Package 1 Height | 2.7 cm |
| Package 1 width | 4.1 cm |
| Package 1 Length | 5 cm |
| Unit Type of Package 2 | S01 |
| Number of Units in Package 2 | 78 |
| Package 2 Weight | 1.294 kg |
| Package 2 Height | 15 cm |
| Package 2 width | 15 cm |
| Package 2 Length | 40 cm |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|