

## Product data sheet

### Characteristics

# LV432593

Long terminal shield, Compact, ComPacT  
NSX400/630, pitch 45mm, IP40, 3 poles



### Main

|                                |   |
|--------------------------------|---|
| Product or component type      | Long terminal shield  |
| Range compatibility            | ComPacT new generation ComPacT NSX400 new generation<br>ComPacT new generation ComPacT NSX630 new generation<br>ComPact ComPact NSX400<br>ComPact ComPact NSX630<br>EasyPact EasyPact CVS400<br>EasyPact EasyPact CVS630<br>PowerPact PowerPact L |
| Accessory / separate part type | Insulation accessories  |
| Poles description              | 3P  |
| Quantity per set               | 1   |



### Complementary

|                         |                              |
|-------------------------|------------------------------|
| Connection pitch        | 45 mm                        |
| IP degree of protection | IP40 conforming to IEC 60529 |

### Packing Units

|                              |            |
|------------------------------|------------|
| Unit Type of Package 1       | PCE        |
| Number of Units in Package 1 | 1          |
| Package 1 Height             | 10.000 cm  |
| Package 1 Width              | 11.000 cm  |
| Package 1 Length             | 17.000 cm  |
| Package 1 Weight             | 251.000 g  |
| Unit Type of Package 2       | S03        |
| Number of Units in Package 2 | 10         |
| Package 2 Height             | 30.000 cm  |
| Package 2 Width              | 30.000 cm  |
| Package 2 Length             | 40.000 cm  |
| Package 2 Weight             | 2.900 kg   |
| Unit Type of Package 3       | P12        |
| Number of Units in Package 3 | 80         |
| Package 3 Height             | 50.000 cm  |
| Package 3 Width              | 80.000 cm  |
| Package 3 Length             | 120.000 cm |
| Package 3 Weight             | 36.056 kg  |

### Offer Sustainability

|                        |  |
|------------------------|--|
| REACH Regulation       |  REACH Declaration  |
| REACH free of SVHC     | Yes  |
| EU RoHS Directive      | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Toxic heavy metal free | Yes  |
| Mercury free           | Yes  |

---

|                            |  |
|----------------------------|--|
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a> |
| RoHS exemption information | <a href="#">Yes</a>                    |

---

### Contractual warranty

---

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

---