

## Product data sheet

### Characteristics

# NSYBRF12PLAG

## 19" fixed chassis, Thalassa, 12U for PLA enclosure H750xW750mm

### Main

|                                    |  |
|------------------------------------|--|
| Range                              | Thalassa                                       |
| Accessory / separate part category | Mounting accessory                             |
| Product or component type          | 19" & nbsp; rack                               |
| Application                        | Multi-purpose                                  |
| For enclosure nominal dimensions   | -  |
| Rack type                          | Fixed  |
| Mounting location                  | Front of enclosure                             |
| Range compatibility                | Thalassa Thalassa PLA<br>Thalassa Thalassa PHD |
| Device composition                 | Fixing elements<br>2 19" uprights              |
| Quantity per set                   | Set of 1                                       |
| Number of units 19"                | 12   |

### Complementary

|                            |                        |
|----------------------------|------------------------|
| Material                   | Sheet steel            |
| Surface finish             | Epoxy-polyester powder |
| Lock type                  | Lock 5 mm double bar   |
| Fixing mode                | By fixing element      |
| Colour                     | Grey (RAL 7035)        |
| Permanent permissible load | 3 kg per unit          |
| Height                     | Nominal: 750 mm        |
| Thickness                  | 2 mm                   |

### Packing Units

|                              |            |
|------------------------------|------------|
| Unit Type of Package 1       | PCE        |
| Number of Units in Package 1 | 1          |
| Package 1 Height             | 10.000 cm  |
| Package 1 Width              | 11.500 cm  |
| Package 1 Length             | 79.000 cm  |
| Package 1 Weight             | 3.986 kg   |
| Unit Type of Package 2       | PAM        |
| Number of Units in Package 2 | 30         |
| Package 2 Height             | 48.000 cm  |
| Package 2 Width              | 100.000 cm |
| Package 2 Length             | 120.000 cm |
| Package 2 Weight             | 132.000 kg |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

|  |  |
|--|--|
| Packaging without single use plastic   | No   |
| Packaging made with recycled cardboard | No   |
| REACH Regulation                       | <a href="#">REACH Declaration</a>                          |
| EU RoHS Directive                      | Pro-active compliance (Product out of EU RoHS legal scope) |
| Mercury free                           | Yes  |
| RoHS exemption information             | <a href="#">Yes</a>  |
| China RoHS Regulation                  | <a href="#">China RoHS Declaration</a>                     |
| Environmental Disclosure               | <a href="#">Product Environmental Profile</a>              |
| Circularity Profile                    | No need of specific recycling operations                   |
| Take-back                              | No   |