


## Product data sheet

### Characteristics

# RZM041FU7

Harmony Electromechanical Relays, Protection module, RC circuit, for all sockets, 110...240V AC



#### Main

Range of product	Harmony Electromechanical Relays
Accessory / separate part category	Protection accessories
Product or component type	Protection module
Accessory / separate part designation	RC circuit
Product compatibility	Socket RSZ (1 C/O)[RETURN]Socket RSZ (2 C/O) [RETURN]Socket RGZ (1 C/O)[RETURN]Socket RGZ (2 C/O)
Product destination	RSB relay
[Uc] control circuit voltage	110...240 V AC
Sale per indivisible quantity	10

#### Complementary

Net weight	0.01 kg
------------	---------

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.000 cm
Package 1 Width	1.200 cm
Package 1 Length	3.100 cm
Package 1 Weight	2.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	3.000 cm
Package 2 Width	7.000 cm
Package 2 Length	11.000 cm
Package 2 Weight	20.000 g
Unit Type of Package 3	S01
Number of Units in Package 3	500
Package 3 Height	15.000 cm
Package 3 Width	15.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	1.300 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------

---

## Wiring Diagram

---

