



### Main

|                           |                 |
|---------------------------|-----------------|
| Range of product          | Standard Series |
| Product or component type | Switched socket |
| Product brand             | Clipsal         |

### Complementary

|                                |                         |
|--------------------------------|-------------------------|
| Control type                   | ON/OFF button           |
| Number of gangs                | 1 gang                  |
| Pin number                     | 3                       |
| Number Of Outlets              | 1                       |
| Actuator                       | Rocker Switch           |
| Mounting Type                  | By screws               |
| Local signalling               | Without light indicator |
| Installation Orientation       | Vertical                |
| Material                       | PC (polycarbonate)      |
| Surface finish                 | Glossy                  |
| [Ue] rated operational voltage | 250 V AC                |
| [In] rated current             | 10 A                    |
| Depth                          | 14 mm                   |
| Length                         | 115 mm                  |
| Width                          | 73 mm                   |
| Mounting Centers               | 84 mm                   |

### Environment

|           |                                                                              |
|-----------|------------------------------------------------------------------------------|
| Standards | AS/NZS 3100<br>AS/NZS 3112<br>AS/NZS 3133<br>AS/NZS 3000:approval number S/1 |
|-----------|------------------------------------------------------------------------------|

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type of Package 1       | PCE     |
| Number of Units in Package 1 | 1       |
| Package 1 Height             | 3 cm    |
| Package 1 Width              | 7.2 cm  |
| Package 1 Length             | 11.5 cm |
| Package 1 Weight             | 70.4 g  |
| Unit Type of Package 2       | BB1     |
| Number of Units in Package 2 | 5       |
| Package 2 Height             | 11.7 cm |
| Package 2 Width              | 10.2 cm |

|                              |         |
|------------------------------|---------|
| Package 2 Length             | 13.8 cm |
| Package 2 Weight             | 450 g   |
| Unit Type of Package 3       | CAR     |
| Number of Units in Package 3 | 100     |
| Package 3 Height             | 25.4 cm |
| Package 3 Width              | 34.8 cm |
| Package 3 Length             | 44.5 cm |
| Package 3 Weight             | 9 kg    |

## Offer Sustainability

|                          |                                                                                                                                 |
|--------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| REACH Regulation         | <a href="#"> REACH Declaration</a>             |
| EU RoHS Directive        | Compliant with Exemptions                                                                                                       |
| China RoHS Regulation    | <a href="#"> China RoHS Declaration</a>        |
| Environmental Disclosure | <a href="#"> Product Environmental Profile</a> |
| Circularity Profile      | No need of specific recycling operations                                                                                        |