

## Product data sheet

### Characteristics

# 5005C305B

## C-Bus Control and Management System, Cable, Category 5e, U/UTP, Solid, LSZH



### Main

Range	C-Bus
Product brand	Clipsal
Product or component type	Cable
Device application	Communication
Colour	Pink
Type of packing	Carton

### Complementary

Type of cable	4 twisted-pairs cable
Bending radius	4 x overall diameter
Communication network category	5e
Transmission frequency	100 MHz
AWG gauge	AWG 24
Cable stiffness	Solid class 1
Cable shielding type	U/UTP
Communication port protocol	1000BASE-T conforming to IEEE 802.3u PoE (Power over Ethernet) conforming to IEEE 802.3af PoE+ (Power over Ethernet) conforming to IEEE 802.3at
Material	Conductor: bare copper Insulation: polyolefin Jacket: Rip cord: polyester multi yarn
Pulling force	110 N
Cable outer diameter	5 Mm +/- 0.2 mm
Length	305 M
Net weight	8.54 Kg

### Environment

Ambient air temperature for installation	0...60 °C
Ambient air temperature for operation	-20...60 °C
Ambient air temperature for storage	-20...60 °C
Directives	2006/95/EC - low voltage directive
Product certifications	CE
Standards	ANSI/TIA-568-C.2:2009 ISO/IEC 11801:ed. 2.2 IEC 61156-5:ed. 2 IEC 60332-1-2 IEC 61034-1 IEC 61034-2 IEC 60754-2

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	19.8 Cm
Package 1 Width	37.8 Cm
Package 1 Length	37.0 Cm
Package 1 Weight	9.52 Kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins