

Product data sheet

Characteristics

PDLO395-BK

Outdoor Socket Switch, Weathershield, Horizontal Twin 10A 250V



Main

Range of product	Iconic
Range	Iconic
Product or component type	Switched socket
Device presentation	Complete product
Product brand	PDL
Outlet poles configuration	1P + E
Outlet standard	Australian
Switch application	On/off switching

Complementary

Socket-outlet type	Twin switched socket-outlet
Control type	Rocker
Device mounting	Wall mounted
Mounting position	Horizontal
Number of power socket outlets	2
Number of rocker	2
Range compatibility	Iconic
Outlet standard description	With earthing contact
Outlet standard deviation	Australian/New Zealand
Pin number	6
Fixing mode	By screw
Installation direction	Horizontal
Surface finish	Matt
Type of packing	Box
Sale per indivisible quantity	1
Rated current	10 A at 250 V AC 50 Hz
Electrical durability	12000 cycles
Connections - terminals	3 screw terminals
Screwdriver shape	Square drive no 1 (SQ1) Philips No 2
Clamping connection capacity	4 x 2.5 mm ² 4 x 4 mm ² 3 x 4 mm ²
Wire stripping length	16 mm
Material	PC (polycarbonate) ABS (acrylonitrile butadiene-styrene) POM (polyoxymethylene)
Type of installation	Outdoor
Height	85 mm
Width	115.5 mm
Depth	70 mm
Product weight	0.24 kg

Environment

Ambient air temperature for storage	0...60 °C
Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %
Standards	AS/NZS 3112
Product certifications	RCM
IP degree of protection	IP54

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.7 cm
Package 1 Width	11.9 cm
Package 1 Length	8.9 cm
Package 1 Weight	252.0 g
Unit Type of Package 2	BB2
Number of Units in Package 2	30
Package 2 Height	30.9 cm
Package 2 Width	41.3 cm
Package 2 Length	45.9 cm
Package 2 Weight	8.56 kg
Unit Type of Package 3	P06
Number of Units in Package 3	360
Package 3 Height	105.0 cm
Package 3 Width	60.0 cm
Package 3 Length	80.0 cm
Package 3 Weight	111.22 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Halogen content performance	Halogen free plastic parts product