

## Product data sheet

### Characteristics

# PDLU2SGY

## PDL Industrial Electrical Accessories, Utility Box, Shallow + Lid 2-Gang IP66, Grey



### Main

|                           |                                       |
|---------------------------|---------------------------------------|
| Range of product          | PDL Industrial Electrical Accessories |
| Product or component type | Enclosure                             |
| Colour tint               | Grey                                  |
| Quantity per set          | Set of 4                              |
| Type of packing           | Carton                                |

### Complementary

|                        |  |
|------------------------|--|
| Material               | PVC (polyvinyl chloride) UV stabilised |
| Surface finish         | Glossy                                 |
| Installation direction | Horizontal<br>Vertical                 |
| Number of gangs        | 2 gangs                                |
| Device mounting        | Surface                                |
| Height                 | 198 mm                                 |
| Width                  | 102 mm                                 |
| Depth                  | 65 mm                                  |
| Fixing center          | 140 x 45 mm                            |

### Packing Units

|                              |            |
|------------------------------|------------|
| Unit Type of Package 1       | PCE        |
| Number of Units in Package 1 | 1          |
| Package 1 Height             | 7.0 cm     |
| Package 1 Width              | 10.1 cm    |
| Package 1 Length             | 19.8 cm    |
| Package 1 Weight             | 473.0 g    |
| Unit Type of Package 2       | CAR        |
| Number of Units in Package 2 | 16         |
| Package 2 Height             | 19.2 cm    |
| Package 2 Width              | 42.4 cm    |
| Package 2 Length             | 42.4 cm    |
| Package 2 Weight             | 7568.0 g   |
| Unit Type of Package 3       | PAL        |
| Number of Units in Package 3 | 320        |
| Package 3 Height             | 96.0 cm    |
| Package 3 Width              | 100.0 cm   |
| Package 3 Length             | 120.0 cm   |
| Package 3 Weight             | 153360.0 g |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

|                            |  |
|----------------------------|--|
| REACH Regulation           | <a href="#">REACH Declaration</a>                          |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) |
| Mercury free               | Yes  |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                     |
| RoHS exemption information | <a href="#">Yes</a>  |