



Osnovne informacije

Grupa proizvoda	TeSys TeSys Deca
Kratko ime uređaja	GVAE
Tip proizvoda ili komponente	Pomoćni kontakti blok
Kompatibilnost proizvoda	GV2L GV3P GV2ME LS1D32 GV3L GV2RT GV2P GV2LE
Lokacija za montiranje	Prednja strana
Raspored kontakata	2 NO
Količina po setu	Set od 10

Dopunske informacije

[ui] nazivni napon izolacije	300 V u skladu sa UL 508 300 V u skladu sa CSA C22.2 No 14 250 V u skladu sa IEC 60947-1
[ue] nazivni radni napon	24...240 V AC 24...60 V DC
[ith] dozvoljena termička struja u vazduhu	2,5 A
Mehanička trajnost	100000 ciklusa
Minimalna struja preklapanja	5 mA
Minimalni napon preklapanja	17 V
Tip zaštite	GG osigurač 10 A GB2CB06 prekidač 10 A
Nazivna snaga u va	120 VA pri 110...120 V AC-15 - električna trajnost: 100000 ciklusa 120 VA pri 230...240 V AC-15 - električna trajnost: 100000 ciklusa 48 VA pri 24 V AC-15 - električna trajnost: 100000 ciklusa 60 VA pri 48 V AC-15 - električna trajnost: 100000 ciklusa
Nazivna snaga u w	15 W pri 48 V DC-13 - električna trajnost: 100000 ciklusa 24 W pri 24 V DC-13 - električna trajnost: 100000 ciklusa 9 W pri 60 V DC-13 - električna trajnost: 100000 ciklusa
Moment pritezanja	1,4 N.m - na vijčani priključni blokovi
Visina	11 mm
Širina	45 mm
Dubina	29 mm
Masa proizvoda	0,02 kg

Okruženje

Karakteristike životne sredine	Normalna sredina
Sertifikacija proizvoda	UKCA

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1,600 cm
Package 1 Width	5,000 cm
Package 1 Length	6,000 cm

Package 1 Weight	19,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	6,300 cm
Package 2 Width	7,300 cm
Package 2 Length	12,000 cm
Package 2 Weight	209,000 g
Unit Type of Package 3	S02
Number of Units in Package 3	220
Package 3 Height	15,000 cm
Package 3 Width	30,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	4,377 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Usaglašeno EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Izjava o zaštiti okoliša	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Informacije O Kraju Radnog Veka
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	18 months
-----------	-----------