

Tehničke karakteristike proizvoda

Karakteristike

A9N26960

podnaponski okidač MN 220-240VAC DC



Osnovne informacije

Grupa proizvoda	Acti 9
Tip proizvoda ili komponente	Podnaponski okidač
Kratko ime uređaja	MN
Napon upravljačkog kola	220...240 V AC 50/60 Hz
Tip upravljanja	Standardni
9 mm redovi	2

Dopunske informacije

Kompatibilnost grupe proizvoda	Acti 9 Acti 9 iDPN Acti 9 Acti 9 C120 Acti 9 Acti 9 C40 Acti 9 Acti 9 C60H-DC Acti 9 Acti 9 C60NA-DC Acti 9 Acti 9 C60PV-DC Acti 9 Acti 9 DPN Vigi Acti 9 Acti 9 DT40 Acti 9 Acti 9 DT60 Acti 9 Acti 9 ID C40 Acti 9 Acti 9 IDc Acti 9 Acti 9 ITG40 Acti 9 Acti 9 ID Acti 9 Acti 9 DPN
Lokalna signalizacija	Indikator akcije
Način montiranja	Fiksno
Nosači za montažu	35 mm simetrična DIN šina
Razvodni blok češljaste sabirnice	Gornji: DA
Visina	82,5 mm
Širina	18 mm
Dubina	73,5 mm
Masa proizvoda	66 g
Boja	Bela
Povezivanje - priključci	Vijčani priključak - 1 kabl(ovi) 2,5 mm ² - fleksibilni Vijčani priključak - 1 kabl(ovi) 2,5 mm ² - kruti Vijčani priključak - 2 kabl(ovi) 1,5 mm ² - fleksibilni Vijčani priključak - 2 kabl(ovi) 1,5 mm ² - kruti
Dužina ogoljenog dela žice	9 mm
Moment pritezanja	1 N.m
Kompatibilnost	MN

Okruženje

Standardi	EN/IEC 60947-5-1
Sertifikacija proizvoda	KEMA[RETURN]ASTA[RETURN]LCIE[RETURN]ASEFA
Tropikalizacija	2 u skladu sa EN/IEC 60947-5-1
Relativna vlažnost	95 % pri 55 °C
Temperatura okoline za rad uređaja	-25...50 °C
Temperatura okoline za skladištenje	-40...85 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3,000 cm
Package 1 Width	7,500 cm
Package 1 Length	9,500 cm
Package 1 Weight	75,600 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	8,500 cm
Package 2 Width	10,000 cm
Package 2 Length	26,500 cm
Package 2 Weight	663,000 g
Unit Type of Package 3	S03
Number of Units in Package 3	72
Package 3 Height	30,000 cm
Package 3 Width	30,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	6,368 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
EU RoHS direktiva	У складу са изузецима
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	 Informacije O Kraju Radnog Veka
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	18 meseci
-----------	-----------