


Tehničke karakteristike proizvoda

Karakteristike

EPH0400369

Asfora - naizmenični prekidač, vijčani
priključak, bez rama, bronza



Osnovne informacije

Seriya	Asfora
Tip proizvoda ili komponente	Prekidač
Prezentacija uređaja	Mehanizam sa montažnim ramom
Broj prekidača	1,0
Funkcija prekidača	Jednopolni naizmenični
Tip opterećenja	Opterećenje za štedljive svjetiljke sa balastom: 100 W
Nijansa boje	Bronzana
Tip pakovanja	Pakovanje u kesicama

Dopunske informacije

Montaža uređaja	Ugradno
Opseg snage	2300 W
Nazivna struja	10 AX pri 250 V AC
Broj kablova	2 kabl(ovi) 2,5 mm ²
Krutost kabla	Fleksibilni Krući Jednožični višezični
Dužina ogoljenog dela žice	13,0 mm
Materijal	ABS (akrilonitril-butadien-stiren)
Završna obrada	Ofarban
Provodni materijal	Bakar
Način fiksiranja	Zavrtnji ili kukice 51...70 mm
Povezivanje - priključci	Vijčani priključci
Širina	71 mm
Visina	71 mm
Dubina	43,0 mm
Projektovana dubina	15 mm
Masa proizvoda	0,0643 kg

Okruženje

Standardi	IEC 60669-1
Sertifikacija proizvoda	VDE
Oznake kvaliteta	CE
Ip stepen zaštite	IP20
Temperatura okoline za rad uređaja	-5...40 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4,0 cm
Package 1 Width	7,0 cm
Package 1 Length	7,0 cm
Package 1 Weight	71,0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9,5 cm
Package 2 Width	18,5 cm
Package 2 Length	27,5 cm
Package 2 Weight	822 g
Unit Type of Package 3	S04
Number of Units in Package 3	120
Package 3 Height	30 cm
Package 3 Width	40 cm
Package 3 Length	60 cm
Package 3 Weight	10,424 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
EU RoHS direktiva	Usaglašeno  EU RoHS Deklaracija
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.