



Main

Range	Acti9
Product name	Acti9 SW
Product or component type	Switch disconnecter
Device short name	SW
Device application	Control
Poles description	4P
Utilisation category	AC-22A

Complementary

[Ie] rated operational current	63 A at 415 V AC 50/60 Hz
[Ue] rated operational voltage	415 V AC 50/60 Hz
Quantity per set	Set of 3
[Icm] rated short-circuit making capacity	0.9 kA switch-disconnector alone
[Icw] rated short-time withstand current	756 A during 300 ms
[Ui] rated insulation voltage	500 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	4 kV conforming to IEC 60947-3
Control type	Toggle
Mounting mode	Fixed
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Downstream: biconnect
9 mm pitches	8
Height	81 mm
Width	72 mm
Depth	74 mm
Net weight	0.48 kg
Colour	White
Mechanical durability	20000 cycles
Electrical durability	10000 cycles
Connections - terminals	Tunnel type terminals (downstream) - 1...35 mm ² - rigid Tunnel type terminals (downstream) - 1...25 mm ² - flexible Tunnel type terminals (upstream) - 1...35 mm ² - rigid Tunnel type terminals (upstream) - 1...25 mm ² - flexible
Wire stripping length	9 mm
Tightening torque	3.5 N.m

Environment

Standards	IEC 60947-3
IP degree of protection	IP20 IP40
Pollution degree	2
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-5...55 °C
Ambient air temperature for storage	-25...85 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.4 cm
Package 1 Width	8 cm
Package 1 Length	8.4 cm
Package 1 Weight	440 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information