

Tehničke karakteristike proizvoda

Karakteristike

14811

češljasta sabirnica - 1P - 125 A / 63 A po
izvodu - D = 432 mm, 16 x 27 mm



Osnovne informacije

Grupa proizvoda	Acti 9
Tip proizvoda ili komponente	Češljasta sabirnica
Način montiranja	Horizontalna
Pribor / posebna kategorija	Pribor za povezivanje
Opis linija	1L
Length in 18 mm modules	24

Dopunske informacije

Broj priključaka	16 priključaka 1 L
Tip razvoda	L
Konfiguracija polova	1 x 1P
Povezivanje	27 mm
Tip priključka	Zupčasti
Udaljenost između terminala	27 mm
Označavanje	L
Izolacija	Izolovano
Prezentacija uređaja	Može se seći
[ie] nazivna radna struja	125 A pri 40 °C
[ue] nazivni napon	500 V AC
[ui] nazivni napon izolacije	500 V AC
Lokacija montaže	Vrh na tunelski priključci Dno na tunelski priključci
9 mm redovi	48
Širina	430 mm
Boja	Bela (RAL 9003)
Kompatibilnost grupe proizvoda	Acti9 Acti 9 NG125 Acti9 Acti 9 C120

Okruženje

Standardi	EN/IEC 61439-1
Otpornost na vatru	960 °C 30 s) u skladu sa IEC 60695-2-1
Stepen zaprljanosti	3

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2,000 cm
Package 1 Width	7,000 cm
Package 1 Length	44,000 cm

Package 1 Weight	105,000 g
Unit Type of Package 2	CAR
Number of Units in Package 2	20
Package 2 Height	12,000 cm
Package 2 Width	11,000 cm
Package 2 Length	103,000 cm
Package 2 Weight	2,410 kg
Unit Type of Package 3	P12
Number of Units in Package 3	80
Package 3 Height	27,000 cm
Package 3 Width	80,000 cm
Package 3 Length	120,000 cm
Package 3 Weight	21,640 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Usaglašeno EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	18 months
-----------	-----------