



Tehničke karakteristike proizvoda Karakteristike

A9N26927 Acti 9 - pomoćni alarmni kontakt SD AC DC



Osnovne informacije

Range of product	Acti 9
Tip proizvoda ili komponente	Kontakt greške
Kratko ime uređaja	SD
Signalni kontakt	1 C/O
[in] nazivna struja	AC-12 3 A at 380...415 V, AC 50/60 Hz AC-12 6 A at 220...240 V, AC 50/60 Hz DC-12 1 A at 130 V, DC DC-12 1,5 A at 60 V, DC DC-12 2 A at 48 V, DC DC-12 6 A at 24 V, DC
9 mm redovi	1
Standardi	EN/IEC 60947-5-1
Sertifikacija proizvoda	ASTA[RETURN]LCIE[RETURN]KEMA[RETURN]ASEFA

Dopunske informacije

Način montiranja	Fiksno
Nosači za montažu	DIN šina
Razvodni blok češljaste sabirnice	Gornji: DA
Visina	85,3 mm
Širina	9 mm
Dubina	73,5 mm
Masa proizvoda	30 g
Boja	Bela
Povezivanje - priključci	Vijčani priključni blok (donji) 2 kabl(ovi) 1,5 mm ² - fleksibilni Vijčani priključni blok (donji) 1 kabl(ovi) 0,5...2,5 mm ² - kruti Vijčani priključni blok (donji) 2 kabl(ovi) 1,5 mm ² - fleksibilni sa kablovskim završetkom
Dužina ogoljenog dela žice	9 mm
Moment pritezanja	1 N.m

Okruženje

Ip stepen zaštite	IP20 conforming to EN/IEC 60947-5-1
Stepen zaprljanosti	3 u skladu sa EN/IEC 60947-5-1
Tropikalizacija	2 u skladu sa EN/IEC 60947-5-1
Temperatura okoline za rad uređaja	-25...50 °C
Temperatura okoline za skladištenje	-40...85 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8,000 cm
Package 1 Width	2,000 cm
Package 1 Length	9,400 cm
Package 1 Weight	38,000 g
Unit Type of Package 2	BB1

Number of Units in Package 2	12
Package 2 Height	8,700 cm
Package 2 Width	10,000 cm
Package 2 Length	26,500 cm
Package 2 Weight	511,000 g
Unit Type of Package 3	S03
Number of Units in Package 3	108
Package 3 Height	30,000 cm
Package 3 Width	30,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	5,084 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACh	REACh Deklaracija
REACh free of SVHC	Yes
EU RoHS direktiva	Usaglašeno EU RoHS Deklaracija
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Izjava o zaštiti životne sredine	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Informacije O Kraju Radnog Veka
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	18 months
-----------	-----------