



Tehničke karakteristike proizvoda

Karakteristike

A9N26947

MX Naponski okidač MX plus 1 OF 48-130Vac dc



Osnovne informacije

Grupa proizvoda	Acti 9
Tip proizvoda ili komponente	Naponski okidač sa OC kontaktom
Kratko ime uređaja	MX + OF
Signalni kontakt	1 C/O
Napon upravljačkog kola	48 V AC 50/60 Hz 48 V DC
9 mm redovi	2

Dopunske informacije

Kompatibilnost grupe proizvoda	Acti9 iDPN Acti9 C120 Acti9 C40 Acti9 C60H-DC Acti9 C60NA-DC Acti9 C60PV-DC Acti9 DPN Vigi Acti9 DT40 Acti9 DT60 Acti9 ID C40 Acti9 IDc Acti9 ITG40 Acti9 ID Acti9 DPN
Lokalna signalizacija	Indikator akcije
Način montiranja	Fiksno
Nosači za montažu	35 mm simetrična DIN šina
Razvodni blok češljaste sabirnice	Gornji: DA
Visina	82,5 mm
Širina	18 mm
Dubina	73,5 mm
Masa proizvoda	65 g
Boja	Bela
Povezivanje - priključci	Vijčani priključak - 1 kabl(ovi) 2,5 mm ² - fleksibilni
Dužina ogoljenog dela žice	9 mm
Moment pritezanja	1 N.m
Kompatibilnost	MX + OF

Okruženje

Standardi	EN/IEC 60947-1
Sertifikacija proizvoda	LCIE[RETURN]ASEFA[RETURN]KEMA[RETURN]ASTA
Tropikalizacija	2 u skladu sa EN/IEC 60947-5-1
Relativna vlažnost	95 % pri 55 °C
Temperatura okoline za rad uređaja	-25...50 °C
Temperatura okoline za skladištenje	-40...85 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2,900 cm
Package 1 Width	7,900 cm
Package 1 Length	9,300 cm
Package 1 Weight	73,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	8,500 cm
Package 2 Width	10,000 cm
Package 2 Length	26,500 cm
Package 2 Weight	640,000 g
Unit Type of Package 3	S03
Number of Units in Package 3	72
Package 3 Height	30,000 cm
Package 3 Width	30,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	6,244 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	REACH Deklaracija
REACH free of SVHC	Yes
EU RoHS direktiva	Usaglašeno EU RoHS Deklaracija
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Izjava o zaštiti životne sredine	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Informacije O Kraju Radnog Veka
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	18 months
-----------	-----------