

Tehničke karakteristike proizvoda

Karakteristike

BVS1000I

SE Easy UPS, 1000VA, Floor/Wall Mount, 230V, 6x IEC C13 outlets, AVR



Pregled

Vreme isporuke	Usually in Stock
----------------	------------------

Osnovne informacije

Tip proizvoda ili komponente	Uređaji za besprekidno napajanje (UPS)
Tip baterije	Olovna baterija

Dopunske informacije

Naponski ulaz	230 V AC
Napon izlaza	230 V AC
Vreme transfera	6 ms tipično : 10 ms maksimalno
Opseg snage	1000 VA 600 W
Električna veza	Ulaz: 1 inlet IEC 320 C14 Izlaz: 6 utičnica IEC 320 C13
Lokalna signalizacija	Alarm, distinctive za nizak nivo baterije Alarm, stalni ili isprekidani ton za preopterećenje LED za status baterije
Vreme punjenja	8 sati
Napon baterije	12 V
Kapacitet baterije	9,0 Ah
Masa proizvoda	5,7 kg
Visina	92,5 mm
Širina	160,5 mm
Dubina	305 mm

Okruženje

Relativna vlažnost	0...90 %, bez kondenzacije
Nadmorska visina za rad	0...6561 ft
Temperatura okoline za rad uređaja	0...40 °C
Standardi	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018
Sertifikacija proizvoda	CE

Fizički

Nosači za montažu	Zid Pod
-------------------	------------

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9,200 cm
Package 1 Width	12,500 cm
Package 1 Length	30,500 cm
Package 1 Weight	5,702 kg
Unit Type of Package 2	S04
Number of Units in Package 2	4
Package 2 Height	30,000 cm
Package 2 Width	40,000 cm
Package 2 Length	60,000 cm
Package 2 Weight	23,458 kg
Unit Type of Package 3	P12
Number of Units in Package 3	32
Package 3 Height	90,000 cm
Package 3 Width	80,000 cm
Package 3 Length	120,000 cm
Package 3 Weight	199,664 kg
SCC14	10731304338380

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	REACH Deklaracija
EU RoHS direktiva	У складу са изузецима
Bez žive	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Izjava o zaštiti okoliša	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Informacije O Kraju Radnog Veka
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.