

Tehničke karakteristike proizvoda

Karakteristike

EPH2900123

Asfora - utičnica - 16A krem



Osnovne informacije

Seriya	Asfora
Tip proizvoda ili komponente	Utičnica
Broj utičnica	1
Konfiguracija polova utičnice	2P + E
Nijansa boje	Krem
Tip pakovanja	Pakovanje u kesicama

Dopunske informacije

Prezentacija uređaja	Kompletan proizvod
Montaža uređaja	Ugradno
Način fiksiranja	Zavrtnji ili kukice 51...69 mm
Standard utičnice	CEE 7/3
Outlet standard deviation	Šuko
Opis standarda utičnice	Uzemljenje sa strane
Opseg snage	3680 W
Nazivna struja	16 A pri 250 V AC
Završna obrada	Sjajno
Materijal	ABS (akrilonitril-butadien-stiren): dekorativni ram ABS + PC: centralna pločica
Dužina ogoljenog dela žice	13,0 mm
Provodni materijal	Bakar
Povezivanje - priključci	Vijčani priključci
Broj kablova	2 kabl(ovi) 2,5 mm ²
Krutost kabla	Fleksibilni Krući Jednožični višežični
Količina po setu	1
Ip stepen zaštite	IP20
Projektovana dubina	10 mm
Širina	83 mm
Visina	83 mm
Dubina	42 mm
Masa proizvoda	0,08 kg

Okruženje





Standardi	IEC 60884-1
Sertifikacija proizvoda	TSE[RETURN]VDE

Informacije navedene u ovoj dokumentaciji predstavljaju opšti opis odnosno tehničke karakteristike performansi proizvoda. Dokumentacija nije namenjena da bude zamena za niti se može koristiti za određivanje prikladnosti i pouzdanosti proizvoda za specifičnu krajnju primenu. Dužnost je korisnika odnosno integratora da izvrši primerenu i sveobuhvatnu analizu rizika, procenu i proveru proizvoda u pogledu odgovarajuće specifične primene ili načina korišćenja. Ni Schneider Electric Industries SAS ni njegova povezana ili zavisna društva neće snositi odgovornost za zloupotrebu ovenavedenih informacija.

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4,000 cm
Package 1 Width	8,500 cm
Package 1 Length	8,500 cm
Package 1 Weight	79,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9,500 cm
Package 2 Width	18,500 cm
Package 2 Length	27,500 cm
Package 2 Weight	869,000 g
Unit Type of Package 3	S04
Number of Units in Package 3	120
Package 3 Height	30,000 cm
Package 3 Width	40,000 cm
Package 3 Length	60,000 cm
Package 3 Weight	11,039 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
EU RoHS direktiva	У складу са изузецима
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	18 meseci
-----------	-----------