

Tehničke karakteristike proizvoda

Karakteristike

EPH3100323

Asfora - utičnica sa uzemljenjem sa strane -
16A poklopac, zaštita IP44 krem



Osnovne informacije

Serija	Asfora
Tip proizvoda ili komponente	Utičnica
Broj utičnica	1
Konfiguracija polova utičnice	2P + E
Dodatne informacije	Poklopac i zaštita
Nijansa boje	Krem
Tip pakovanja	Pakovanje u kesicama

Dopunske informacije

Prezentacija uređaja	Kompletan proizvod
Montaža uređaja	Ugradno
Način fiksiranja	Zavrtnji ili kukice 51...69 mm
Standard utičnice	CEE 7/3
Outlet standard deviation	Šuko
Opis standarda utičnice	Uzemljenje sa strane
Opseg snage	3680 W
Nazivna struja	16 A pri 250 V AC
Završna obrada	Sjajno
Materijal	ABS (akrilonitril-butadien-stiren): dekorativni ram ABS + PC: centralna pločica ABS (akrilonitril-butadien-stiren): poklopac
Dužina ogoljenog dela žice	13,0 mm
Provodni materijal	Bakar
Povezivanje - priključci	Vijčani priključci
Broj kablova	2 kabl(ovi) 2,5 mm ²
Krutost kabla	Fleksibilni Krući Jednožični višežični
Količina po setu	1
Ip stepen zaštite	IP44
Projektovana dubina	17 mm
Širina	83 mm
Visina	83 mm
Dubina	48 mm
Masa proizvoda	0,104 kg

Okruženje

Standardi	IEC 60884-1
Sertifikacija proizvoda	TSE[RETURN]VDE[RETURN]Aenor

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5,000 cm
Package 1 Width	8,500 cm
Package 1 Length	8,500 cm
Package 1 Weight	104,500 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9,500 cm
Package 2 Width	18,500 cm
Package 2 Length	27,500 cm
Package 2 Weight	1,121 kg
Unit Type of Package 3	S04
Number of Units in Package 3	120
Package 3 Height	30,000 cm
Package 3 Width	40,000 cm
Package 3 Length	60,000 cm
Package 3 Weight	14,076 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	REACH Deklaracija
EU RoHS direktiva	У складу са изузецима
Bez žive	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Profil cirkularnosti	Informacije O Kraju Radnog Veka
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	18 months
-----------	-----------