

# Tehničke karakteristike proizvoda

## Karakteristike

# LV429407

## podnaponski okidač MN - 208..277V 60Hz, 220..240V 50/60Hz



### Osnovne informacije

Grupa proizvoda	ComPacT
Grupa proizvoda	ComPacT NSX100...250 ComPacT NSX100...250 nova generacija ComPacT NSX400...630 ComPacT NSX400...630 nova generacija ComPacT NSX100...250 DC ComPacT NSX100...250 DC nova generacija ComPacT NSX100...250 DC PV ComPacT NSX100...250 DC PV nova generacija ComPacT NSX400...630 DC ComPacT NSX400...630 DC nova generacija ComPacT NSX400...630 DC PV ComPacT NSX400...630 DC PV nova generacija
Kratko ime uređaja	MN
Tip proizvoda ili komponente	Naponski okidač
Primena uređaja	Upravljanje
Tip naponskog okidača	Kalem za isključenje Podnaponski okidač
Napon upravljačkog kola	220...240 V AC 50/60 Hz 208...277 V AC 60 Hz
Kompatibilnost grupe proizvoda	ComPacT nova generacija (Compact NSX nova generacija) ComPacT nova generacija (ComPacT NSX DC nova generacija) Compact (Compact NSX) Compact (Compact NSX DC) Easypact (EasyPact CVS) PowerPact (PowerPact Multistandard)

### Dopunske informacije

Operating threshold	0.35...0.7 x Un otvaranje 0.85 x Un zatvaranje
Vreme odziva	50 ms
Snaga držanja	5 VA
Udarna snaga napajanja	10 VA
Pomoćni priključni blok	Opruga 0,5...1,5 mm <sup>2</sup> (AWG 20...AWG 16)
Dužina ogoljenog dela žice	7 mm

### Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4,5 cm
Package 1 Width	4,6 cm
Package 1 Length	6,0 cm
Package 1 Weight	120,0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	7,2 cm
Package 2 Width	10,4 cm

Package 2 Length	23,5 cm
Package 2 Weight	1,252 kg
Unit Type of Package 3	S03
Number of Units in Package 3	60
Package 3 Height	30,0 cm
Package 3 Width	30,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	7,896 kg

## Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	<a href="#">REACH Deklaracija</a>
EU RoHS direktiva	Usaglašeno <a href="#">EU RoHS Deklaracija</a>
Bez žive	Da
RoHS regulativa za Kinu	<a href="#">RoHS Deklaracija Za Kinu</a>
Informacije o RoHS izuzecima	<a href="#">Da</a>
Izjava o zaštiti okoliša	<a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>
Profil cirkularnosti	<a href="#">Informacije O Kraju Radnog Veka</a>
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.
Bez PVC	Da

## Ugovorna garancija

Garancija	18 months
-----------	-----------