

Tehničke karakteristike proizvoda

Karakteristike

MGU7.002

Unica - univerzalni montažni ram - zamak- 2 m
- jednostruki



Osnovne informacije

Range of product	Unica
Pribor / posebna kategorija	Pribor za montažu
Tip proizvoda ili komponente	Montažni ram
Ime dekorativnog elementa	Unica
Prezentacija uređaja	Montažni ram
Broj modula	2 modula (jednostruki)
Broj dvostrukih modula	Jednostruki
Način pričvršćivanja	Zavrtnjima

Dopunske informacije

Nosači za montažu	Univerzalno
Materijal	Zamak
Standardi	EN 60669-1
Dubina	7 mm
Širina	75 mm
Visina	71 mm
Masa proizvoda	0,034 kg

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0,500 cm
Package 1 Width	7,500 cm
Package 1 Length	7,500 cm
Package 1 Weight	25,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	70
Package 2 Height	12,000 cm
Package 2 Width	12,500 cm
Package 2 Length	18,500 cm
Package 2 Weight	1,822 kg
Unit Type of Package 3	S02
Number of Units in Package 3	280
Package 3 Height	15,000 cm
Package 3 Width	30,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	7,523 kg

Informacije navedene u ovoj dokumentaciji predstavljaju opšti opis odnosno tehničke karakteristike performansi proizvoda. Dokumentacija nije namenjena da bude zamena za niti se može koristiti za određivanje prikladnosti i pouzdanosti proizvoda za specifičnu krajnju primenu. Dužnost je korisnika odnosno integratora da izvrši primerenu i sveobuhvatnu analizu rizika, procenu i proveru proizvoda u pogledu odgovarajuće specifične primene ili načina korišćenja. Ni Schneider Electric Industries SAS ni njegova povezana ili zavisna društva neće snositi odgovornost za zloupotrebu ovdenavedenih informacija.

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACh	REACh Deklaracija
REACh bez SVHC	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) EU RoHS deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Izjava o zaštiti okoliša	Profil Ekološke Prihvatljivosti Proizvoda

Ugovorna garancija

Garancija	18 meseci
-----------	-----------