



Osnovne informacije

Range of product	Acti 9
Tip proizvoda ili komponente	OC kontakt
Kratko ime uređaja	iOF
Signalni kontakt	1 C/O
[in] nazivna struja	AC-12 6 A at 240 V, AC 50/60 Hz AC-12 3 A at 415 V, AC 50/60 Hz DC-12 2 A at 48 V, DC DC-12 1,5 A at 60 V, DC DC-12 1 A at 130 V, DC DC-12 6 A at 24 V, DC
9 mm redovi	1

Dopunske informacije

[ui] nazivni napon izolacije	500 V
[uimp] nazivni podnosivi impulsni napon	4 kV
Način montiranja	Sistemom na klik
Nosači za montažu	DIN šina
Razvodni blok češljaste sabirnice	Gornji: DA
Visina	86 mm
Širina	9 mm
Dubina	73 mm
Masa proizvoda	32 g
Boja	Bela
Povezivanje - priključci	Vijčani priključni blok (donji) 1 kabl(ovi) 1...4 mm ² - kruti Vijčani priključni blok (donji) 1 kabl(ovi) 0,5...2,5 mm ² - fleksibilni Vijčani priključni blok (donji) 2 kabl(ovi) 2,5 mm ² - kruti Vijčani priključni blok (donji) 2 kabl(ovi) 1,5 mm ² - fleksibilni sa kablovskim završetkom
Dužina ogoljenog dela žice	10 mm
Moment pritezanja	1 N.m

Okruženje

Standardi	EN/IEC 60947-5-1
Ip stepen zaštite	IP20 conforming to EN/IEC 60947-5-1
Stepen zaprljanosti	3 u skladu sa EN/IEC 60947-5-1
Tropikalizacija	2 u skladu sa EN/IEC 60947-5-1
Temperatura okoline za rad uređaja	-35...70 °C
Temperatura okoline za skladištenje	-40...85 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7,800 cm
Package 1 Width	2,000 cm
Package 1 Length	9,200 cm
Package 1 Weight	40,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	12

Package 2 Height	8,500 cm
Package 2 Width	10,000 cm
Package 2 Length	27,200 cm
Package 2 Weight	570,000 g
Unit Type of Package 3	S03
Number of Units in Package 3	120
Package 3 Height	30,000 cm
Package 3 Width	30,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	6,350 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Usaglašeno  EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	 Informacije O Kraju Radnog Veka
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	18 meseci
-----------	-----------