

Tehničke karakteristike proizvoda

Karakteristike

LA9ZA32434

montažna ploča LA9Z 1x3P 32A - 45x200x63mm za GV2LE/P/ME+LC1D



Osnovne informacije

Grupa proizvoda	Linergy
Ime proizvoda	BZ
Kratko ime uređaja	LA9Z
Tip proizvoda ili komponente	Adapteri za sabirničke sisteme
Broj priključaka	1 priključak
Količina po setu	Set od 4

Dopunske informacije

Kompatibilnost grupe proizvoda	Prisma G Prisma P Prisma PH Prisma Pack TeSys GV2 TeSys D Spacial
Kompatibilnost proizvoda	GV2LE GV2P LC1D GV2ME
Broj polova	3P
Dopustiva struja	32 A
[ui] nazivni napon izolacije	690 V
Poprečni presek kabla	6 mm ² - AWG 10
Odstojanje izvoda sabirnica	60 mm
Širina	45 mm
Visina	200 mm
Dubina	63 mm
Boja	Siva

Okruženje

IP stepen zaštite	IP20 u skladu sa IEC 60529
-------------------	----------------------------

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13,000 cm
Package 1 Width	11,500 cm
Package 1 Length	22,500 cm
Package 1 Weight	267,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	4

Package 2 Height	13,000 cm
Package 2 Width	11,500 cm
Package 2 Length	22,500 cm
Package 2 Weight	1,141 kg
Unit Type of Package 3	S03
Number of Units in Package 3	24
Package 3 Height	30,000 cm
Package 3 Width	30,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	7,324 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Usaglašeno  EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.
Učinak u vezi sa sadržajem halogena	Proizvod sa plastičnim delovima bez halogena