

# Tehničke karakteristike proizvoda

## Karakteristike

# NU172418

## Ugradna kutija 2 kolone bela



### Osnovne informacije

Grupa proizvoda	New Unica
Tip proizvoda ili komponente	Radna stanica
Broj modula	2 x 4 modula
Pozicija montiranja ručice	Vertikalno
Način pričvršćivanja	Embedment Kukicama

### Dopunske informacije

Zaštitna oprema	Montažni ram Ram
Montaža uređaja	Ugradno
Kablovski uvod	5 definisani otvori 20 mm for diameter 5 definisani otvori 25 mm for diameter 2 dno cable entries 50 x 35 mm for size 20 mm for diameter 2 dno cable entries 50 x 35 mm for size 25 mm for diameter
Otpornost na vatru	850 °C, vreme gašenja <30 sekundi
Materijal	ABS (akrilonitril-butadien-stiren): separator PC: kutija ABS (akrilonitril-butadien-stiren): dekorativni ram
Dubina	62 mm
Širina	165 mm
Visina	165 mm
Masa proizvoda	0,278 kg
Otpornost na hemijske supstance	Otporan na alkohol (70%) Otporan na alkohol (96%) Otporan na A-mlečnu kiselinu Otporan na razblaženi kvarterni amonijum Otporan na razblaženo izbeljivač Otporan na razblažen amonijak Otporan na vodu sa sapunom Otporan na čistač kristala Otporan na vodonik peroksid 10 zapremina Otporan na heksan

### Okruženje

Ik stepen zaštite	IK04
-------------------	------

### Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7,9 cm
Package 1 Width	17,9 cm
Package 1 Length	18,6 cm
Package 1 Weight	382,0 g

Unit Type of Package 2	S04
Number of Units in Package 2	20
Package 2 Height	30,0 cm
Package 2 Width	40,0 cm
Package 2 Length	60,0 cm
Package 2 Weight	8,663 kg
Unit Type of Package 3	P06
Number of Units in Package 3	80
Package 3 Height	77,0 cm
Package 3 Width	80,0 cm
Package 3 Length	60,0 cm
Package 3 Weight	43,152 kg

## Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	<a href="#">REACH Deklaracija</a>
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) <a href="#">EU RoHS deklaracija</a>
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	<a href="#">RoHS Deklaracija Za Kinu</a>
Informacije o RoHS izuzecima	<a href="#">Da</a>
Izjava o zaštiti okoliša	<a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
Minimum percentage of recycled plastic content	21