



### Osnovne informacije

Grupa proizvoda	New Unica
Tip proizvoda ili komponente	Telefonska utičnica
Primena uređaja	Komunikacija
Prezentacija uređaja	Mehanizam
Nijansa boje	Aluminijum
Tip telefonske utičnice	RJ12 (6 kontakti) - kategorija 3 pri 16 Mbit/s

### Dopunske informacije

Broj utičnica	1
Broj modula	1 modul
Povezivanje - priključci	Vijčani priključci upredene parice
Montaža uređaja	Ugradno
Način fiksiranja	Utično
Materijal	Termoplastika ABS-UV stabilizovana: centralna pločica
Dubina	34 mm
Širina	22,5 mm
Visina	45 mm
Dubina za ugradnju	34 mm
Temperatura okoline za rad uređaja	-25...55 °C
Temperatura okoline za skladištenje	-25...55 °C
Otpornost na hemijske supstance	Otporan na alkohol (70%) Otporan na alkohol (96%) Otporan na A-mlečnu kiselinu Otporan na razblaženi kvarterni amonijum Otporan na razblaženo izbeljivač Otporan na razblažen amonijak Otporan na vodu sa sapunom Otporan na čistač kristala Otporan na vodonik peroksid 10 zapremina Otporan na heksan

### Okruženje

Ip stepen zaštite	IP20
Ik stepen zaštite	IK01

### Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2,3 cm
Package 1 Width	3,4 cm
Package 1 Length	4,5 cm
Package 1 Weight	13,0 g

Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	5,5 cm
Package 2 Width	14,0 cm
Package 2 Length	26,0 cm
Package 2 Weight	130,0 g
Unit Type of Package 3	S01
Number of Units in Package 3	20
Package 3 Height	15,0 cm
Package 3 Width	15,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	464,0 g

## Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	<a href="#">REACH Deklaracija</a>
REACH bez SVHC	Da
EU RoHS direktiva	Usaglašeno <a href="#">EU RoHS Deklaracija</a>
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	<a href="#">RoHS Deklaracija Za Kinu</a>
Informacije o RoHS izuzecima	<a href="#">Da</a>
Izjava o zaštiti okoliša	<a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.