



Tehničke karakteristike proizvoda

Karakteristike

83921

Mureva modularno kućište - 1 utičnica sa otcepnom kutijom - 103x360

Osnovne informacije

Grupa proizvoda	Mureva
Ime proizvoda	Mureva Enclosure
Tip proizvoda ili komponente	Orman
Tip ormara	Modularna baza

Dopunske informacije

Način montiranja	Montaža na površini
Broj otvora interfejsa	1
Kablovski uvod	Vodilica Definisani otvor
Materijal	Samogasivi polimer: kućište
Masa proizvoda	0,567 kg
Dimenzija baze	103 x 225 mm
Visina	350 mm
Širina	105 mm
Dubina	70 mm
Boja	Siva (RAL 7035)

Okruženje

Standardi	IEC 60695-2-1 EN 62262 EN 60439 IEC 60529
Ip stepen zaštite	IP65 conforming to IEC 60529
Ik stepen zaštite	IK09 conforming to EN 62262
Otpornost na vatru	650 °C u skladu sa IEC 60695-2-1

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11,300 cm
Package 1 Width	10,800 cm
Package 1 Length	37,000 cm
Package 1 Weight	490,000 g
Unit Type of Package 2	CAR
Number of Units in Package 2	6
Package 2 Height	39,300 cm
Package 2 Width	35,900 cm
Package 2 Length	24,300 cm

Package 2 Weight	3,345 kg
Unit Type of Package 3	P12
Number of Units in Package 3	132
Package 3 Height	120,000 cm
Package 3 Width	80,000 cm
Package 3 Length	77,000 cm
Package 3 Weight	90936,000 kg

Održivost ponude

Pakovanje bez plastike	Ne
Pakovanje sa recikliranim kartonom	Da
Uredba REACh	REACh Deklaracija
Bez SVHC-a REACh	Da
EU RoHS direktiva	Usaglašeno EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
Informacije o izuzeću od RoHS	Da
Kina RoHS regulacija	RoHS Deklaracija Za Kinu
Izjava o zaštiti okoline	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Proizvod se mora odložiti na tržišta Evropske unije nakon posebnog sakupljanja otpada i nikada ne završiti u kanti za smeće
Povraćaj	No
Emisija ugljenika (kg CO2 eq.)	4

Ugovorna garancija

Garancija	18 meseci
-----------	-----------