



# Tehničke karakteristike proizvoda Karakteristike

## EPH1500369 Asfora naizmenični prekidač sa lokat.lampicom vijčani priklj.,bez rama,bronz

### Osnovne informacije

Serija	Asfora
Tip proizvoda ili komponente	Prekidač
Prezentacija uređaja	Mehanizam sa montažnim ramom
Broj prekidača	1
Funkcija prekidača	Jednopolni naizmenični
Tip opterećenja	Opterećenje za štedljive svetiljke sa balastom: 100 W
Nijansa boje	Bronzana
Tip pakovanja	Pakovanje u kesicama

### Dopunske informacije

Montaža uređaja	Ugradno
Lokalna signalizacija	LED
Opseg snage	2300 W
Nazivna struja	10 AX pri 250 V AC
Broj kablova	2 kabl(ovi) 2,5 mm <sup>2</sup>
Krutost kabla	Fleksibilni Krući Jednožični višezični
Dužina ogoljenog dela žice	13,0 mm
Materijal	ABS (akrilonitril-butadien-stiren)
Završna obrada	Ofarban
Provodni materijal	Bakar
Način fiksiranja	Zavrtnji ili kukice51...70 mm
Povezivanje - priključci	Vijčani priključci
Širina	71 mm
Visina	71 mm
Dubina	43,0 mm
Projektovana dubina	15 mm
Masa proizvoda	0,0666 kg

### Okruženje

Standardi	IEC 60669-1
Sertifikacija proizvoda	VDE
Oznake kvaliteta	CE
Ip stepen zaštite	IP20
Temperatura okoline za rad uređaja	-5...40 °C

Informacije navedene u ovoj dokumentaciji predstavljaju opšti opis odnosno tehničke karakteristike performansi proizvoda. Dokumentacija nije namenjena da bude zamena za niti se može koristiti za određivanje prikladnosti i pouzdanosti proizvoda za specifičnu krajnju primenu. Dužnost je korisnika odnosno integratora da izvrši primerenu i sveobuhvatnu analizu rizika, procenu i proveru proizvoda u pogledu odgovarajuće specifične primene ili načina korišćenja. Ni Schneider Electric Industries SAS ni njegova povezana ili zavisna društva neće snositi odgovornost za zloupotrebu ovenavedenih informacija.

## Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4,500 cm
Package 1 Width	7,000 cm
Package 1 Length	7,000 cm
Package 1 Weight	66,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9,500 cm
Package 2 Width	18,500 cm
Package 2 Length	27,500 cm
Package 2 Weight	740,000 g
Unit Type of Package 3	S04
Number of Units in Package 3	120
Package 3 Height	30,000 cm
Package 3 Width	40,000 cm
Package 3 Length	60,000 cm
Package 3 Weight	9,531 kg

## Održivost ponude

Pakovanje sa recikliranim kartonom	Da
Uredba REACH	<a href="#">REACH Deklaracija</a>
EU RoHS direktiva	Usaglašeno sa izuzecima
Bez žive	Da
Informacije o izuzeću od RoHS	<a href="#">Da</a>
Kina RoHS regulacija	<a href="#">RoHS Deklaracija Za Kinu</a>
Izjava o zaštiti okoline	<a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Proizvod se mora odložiti na tržišta Evropske unije nakon posebnog sakupljanja otpada i nikada ne završiti u kanti za smeće