

# Tehničke karakteristike proizvoda

## Karakteristike

# NU124418

## Nadgradna kutija 4 kolone bela



### Osnovne informacije

Grupa proizvoda	New Unica
Tip proizvoda ili komponente	Radna stanica
Broj modula	4 x 4 modules
Pozicija montiranja ručice	Vertikalno
Način pričvršćivanja	Zavrtnjima

### Dopunske informacije

Zaštitna oprema	Montažni ram Ram
Montaža uređaja	Nadgradno
Kablovski uvod	5 odvojive ploče 2 dno cable entries 20 mm for diameter 2 dno cable entries 25 mm for diameter 2 dno cable entries 45 mm for diameter
Materijal	ABS (akrilonitril-butadien-stiren): kutija ABS (akrilonitril-butadien-stiren): separator ABS (akrilonitril-butadien-stiren): dekorativni ram
Dubina	60 mm
Širina	300 mm
Visina	165 mm
Masa proizvoda	0,635 kg
Otpornost na hemijske supstance	Otporan na alkohol (70%) Otporan na alkohol (96%) Otporan na A-mlečnu kiselinu Otporan na razblaženi kvarterni amonijum Otporan na razblaženo izbeljivač Otporan na razblažen amonijak Otporan na vodu sa sapunom Otporan na čistač kristala Otporan na vodonik peroksid 10 zapremina Otporan na heksan

### Okruženje

Ik stepen zaštite	IK04
-------------------	------

### Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7,9 cm
Package 1 Width	18,0 cm
Package 1 Length	31,6 cm
Package 1 Weight	745,0 g
Unit Type of Package 2	S04

Number of Units in Package 2	10
Package 2 Height	30,0 cm
Package 2 Width	40,0 cm
Package 2 Length	60,0 cm
Package 2 Weight	8,21 kg
Unit Type of Package 3	P06
Number of Units in Package 3	40
Package 3 Height	77,0 cm
Package 3 Width	80,0 cm
Package 3 Length	60,0 cm
Package 3 Weight	41,26 kg

## Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACh	<a href="#">REACH Deklaracija</a>
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) <a href="#">EU RoHS deklaracija</a>
Bez toksičnih teških metala	Da
Bez žive	Da
Sustainable packaging	Yes
RoHS regulativa za Kinu	<a href="#">RoHS Deklaracija Za Kinu</a>
Informacije o RoHS izuzecima	<a href="#">Da</a>
Izjava o zaštiti okoliša	<a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja