

# Tehničke karakteristike proizvoda

## Karakteristike

# NU200418

## Ram dek. Unica Studio 2 elementa beli



### Osnovne informacije

Grupa proizvoda	New Unica
Primena uređaja	Montaža
Tip proizvoda ili komponente	Dekorativni ram
Ime dekorativnog elementa	Unica Studio
Broj dvostrukih modula	Dvostruki
Pravac instalacije	Horizontalno vertikalno
Tip prekidača	Double
Broj modula	2 x 2 modula
Način pričvršćivanja	Utično
Nijansa boje	Bela (RAL 9003)

### Dopunske informacije

Materijal	Termoplastika ABS-UV stabilizovana: dekorativni ram
Završna obrada	Sjajno
Standardi	IEC 60884-1 IEC 60669-1
Širina	156 mm
Visina	85 mm
Dubina	10 mm
Masa proizvoda	0,021 kg
Otpornost na hemijske supstance	Otporan na alkohol (70%) Otporan na alkohol (96%) Otporan na A-mlečnu kiselinu Otporan na razblaženi kvarterni amonijum Otporan na razblaženo izbeljivač Otporan na razblažen amonijak Otporan na vodu sa sapunom Otporan na čistač kristala Otporan na vodonik peroksid 10 zapremina Otporan na heksan

### Okruženje

Ik stepen zaštite	IK04
Ip stepen zaštite	IP21 D

### Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1,000 cm
Package 1 Width	8,500 cm
Package 1 Length	15,600 cm
Package 1 Weight	24,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	12,700 cm

Package 2 Width	12,000 cm
Package 2 Length	18,500 cm
Package 2 Weight	317,000 g
Unit Type of Package 3	S04
Number of Units in Package 3	180
Package 3 Height	30,000 cm
Package 3 Width	40,000 cm
Package 3 Length	60,000 cm
Package 3 Weight	6,485 kg

## Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	<a href="#">REACH Deklaracija</a>
REACH bez SVHC	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) <a href="#">EU RoHS deklaracija</a>
Bez toksičnih teških metala	Da
Bez žive	Da
Sustainable packaging	Yes
RoHS regulativa za Kinu	<a href="#">RoHS Deklaracija Za Kinu</a>
Informacije o RoHS izuzecima	<a href="#">Da</a>
Izjava o zaštiti okoliša	<a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja