

# Tehničke karakteristike proizvoda

## Karakteristike

# NU201018

## Ram dek. Unica Studio 5 elemenata beli



### Osnovne informacije

Grupa proizvoda	New Unica
Primena uređaja	Montaža
Tip proizvoda ili komponente	Dekorativni ram
Ime dekorativnog elementa	Unica Studio
Broj dvostrukih modula	Petostruki
Pravac instalacije	Horizontalno vertikalno
Tip prekidača	Quintuple
Broj modula	5 x 2 modules
Način pričvršćivanja	Utično
Nijansa boje	Bela (RAL 9003)

### Dopunske informacije

Materijal	Termoplastika ABS-UV stabilizovana: dekorativni ram
Standardi	IEC 60669-1 IEC 60884-1
Širina	369 mm
Visina	85 mm
Dubina	10 mm
Masa proizvoda	0,047 kg
Otpornost na hemijske supstance	Otporan na alkohol (70%) Otporan na alkohol (96%) Otporan na A-mlečnu kiselinu Otporan na razblaženi kvarterni amonijum Otporan na razblaženo izbeljivač Otporan na razblažen amonijak Otporan na vodu sa sapunom Otporan na čistač kristala Otporan na vodonik peroksid 10 zapremina Otporan na heksan

### Okruženje

Ik stepen zaštite	IK04
Ip stepen zaštite	IP21 D

### Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1,000 cm
Package 1 Width	8,500 cm
Package 1 Length	37,000 cm
Package 1 Weight	54,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	7,500 cm
Package 2 Width	9,500 cm

Package 2 Length	38,200 cm
Package 2 Weight	344,000 g
Unit Type of Package 3	S04
Number of Units in Package 3	105
Package 3 Height	30,000 cm
Package 3 Width	40,000 cm
Package 3 Length	60,000 cm
Package 3 Weight	8,023 kg

## Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	<a href="#">REACH Deklaracija</a>
REACH bez SVHC	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) <a href="#">EU RoHS deklaracija</a>
Bez toksičnih teških metala	Da
Bez žive	Da
Sustainable packaging	Yes
RoHS regulativa za Kinu	<a href="#">RoHS Deklaracija Za Kinu</a>
Informacije o RoHS izuzecima	<a href="#">Da</a>
Izjava o zaštiti okoliša	<a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja