



# Tehničke karakteristike proizvoda Karakteristike

## NU280455M Ram dek. Unica Studio 2 E zlatni/krem

### Osnovne informacije

Grupa proizvoda	New Unica
Primena uređaja	Montaža
Tip proizvoda ili komponente	Dekoratívni ram
Ime dekorativnog elementa	Unica Studio Metal
Broj dvostrukih modula	Dvostruki
Pravac instalacije	Horizontalno vertikalno
Tip prekidača	Double
Broj modula	2 x 2 modula
Način pričvršćivanja	Zavrtnjima
Nijansa boje	White aluminium
Side color	Bela (RAL 9003)

### Dopunske informacije

Materijal	Polikarbonat: međuploča
Završna obrada	Brušena završna obrada
Količina po setu	Set od 3
Standardi	IEC 60669-1 IEC 60884-1
Širina	156 mm
Visina	85 mm
Dubina	10 mm
Masa proizvoda	0,033 kg
Otpornost na hemijske supstance	Otporan na alkohol (70%) Otporan na alkohol (96%) Otporan na A-mlečnu kiselinu Otporan na razblaženi kvarterni amonijum Otporan na razblaženo izbeljivač Otporan na razblažen amonijak Otporan na vodu sa sapunom Otporan na čistač kristala Otporan na vodonik peroksid 10 zapremina Otporan na heksan

### Okruženje

Ik stepen zaštite	IK04
Ip stepen zaštite	IP21 D

### Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1,000 cm
Package 1 Width	8,700 cm
Package 1 Length	16,000 cm
Package 1 Weight	35,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	3

Package 2 Height	6,600 cm
Package 2 Width	12,800 cm
Package 2 Length	19,000 cm
Package 2 Weight	163,000 g
Unit Type of Package 3	S04
Number of Units in Package 3	108
Package 3 Height	30,000 cm
Package 3 Width	40,000 cm
Package 3 Length	60,000 cm
Package 3 Weight	6,658 kg

## Održivost ponude

Pakovanje bez plastike	Ne
Pakovanje sa recikliranim kartonom	Da
Uredba REACH	<a href="#">REACH Deklaracija</a>
Bez SVHC-a REACH	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) <a href="#">EU RoHS deklaracija</a>
Bez toksičnih teških metala	Da
Bez žive	Da
Održivo pakovanje	Da
Informacije o izuzeću od RoHS	<a href="#">Da</a>
Kina RoHS regulacija	<a href="#">RoHS Deklaracija Za Kinu</a>
Izjava o zaštiti okoline	<a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
Povraćaj	No
Emisija ugljenika (kg CO2 eq.)	1