



Main

Range of product	Acti9
Product or component type	Undervoltage release
Device short name	iMNx
[Uc] control circuit voltage	220...240 V AC 50/60 Hz
Control type	With external feeding
9 mm pitches	2

Complementary

Range compatibility	Acti 9 Acti9 iC65 Acti 9 Acti9 ARA Acti 9 Acti9 iDPN Vigi Acti 9 Acti9 iID Acti 9 Acti9 iSW-NA Acti 9 Acti9 RCA Acti 9 Acti9 iDPN (China version) Acti 9 Acti9 iC60 double terminals miniature circuit breaker Acti 9 Acti9 iC40
Local signalling	Action indicator
Mounting mode	Clip-on
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Top: YES
Width	18 mm
Colour	White
Connections - terminals	Clamp terminal - 1 cable(s) 11 mm ² - rigid Clamp terminal - 2 cable(s) 2.1 mm ² - rigid Clamp terminal - 1 cable(s) 9 mm ² - flexible Clamp terminal - 2 cable(s) 2.1 mm ² - flexible with cable end
Tightening torque	1 N.m
Compatibility code	IMNx

Environment

Standards	EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	8.1 cm
Package 1 Length	9.3 cm
Package 1 Weight	88 g

Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	8.8 cm
Package 2 Width	10.4 cm
Package 2 Length	26.7 cm
Package 2 Weight	758 g
Unit Type of Package 3	S03
Number of Units in Package 3	72
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	7.311 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------