

# Tehničke karakteristike proizvoda

## Karakteristike

# NU347818

## Dvost. utičnica RJ45 CAT5 UTP 45x90 bela



### Osnovne informacije

Grupa proizvoda	New Unica
Tip proizvoda ili komponente	Komunikacione utičnice
Primena uređaja	Komunikacija
Prezentacija uređaja	Mehanizam
Nijansa boje	Bela (RAL 9003)
Tip komunikacione utičnice	RJ45 8 kontakt(i) kat.5e < 155 MHz
Zaštitna oprema	Nosač oznake Zaštitni poklopac

### Dopunske informacije

Tip komunikacione mreže	1000BASE-T
Protokol komunikacionog porta	ATM 155 Mbps
Broj modula	4 modula
Broj utičnica	2
Tip dizajna	Infraplus
Tip priključka	S-One
Tip oklopa kabla	U/UTP
Način formiranja kabla	Neoklopljen kabl sa upredenim paricama
Povezivanje - priključci	Na klik
Montaža uređaja	Ugradno
Način fiksiranja	Utično
Pravac instalacije	Ravno
Materijal	Termoplastika ABS-UV stabilizovana: centralna pločica
Dubina	40,5 mm
Širina	45 mm
Visina	90 mm
Dubina za ugradnju	40,5 mm
Otpornost na hemijske supstance	Otporan na alkohol (70%) Otporan na alkohol (96%) Otporan na A-mlečnu kiselinu Otporan na razblaženi kvarterni amonijum Otporan na razblaženo izbeljivač Otporan na razblažen amonijak Otporan na vodu sa sapunom Otporan na čistač kristala Otporan na vodonik peroksid 10 zapremina Otporan na heksan

### Okruženje

Ip stepen zaštite	IP20
Ik stepen zaštite	IK01
Temperatura okoline za rad	-25...55 °C
Temperatura okoline za skladištenje	-25...55 °C

## Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7,5 cm
Package 1 Width	8,0 cm
Package 1 Length	9,6 cm
Package 1 Weight	75,0 g
Unit Type of Package 2	S03
Number of Units in Package 2	38
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	3,212 kg
Unit Type of Package 3	P06
Number of Units in Package 3	304
Package 3 Height	77 cm
Package 3 Width	80 cm
Package 3 Length	60 cm
Package 3 Weight	34,196 kg

## Održivost ponude

Status održive ponude	Green Premium proizvod
REACH bez SVHC	Da
EU RoHS direktiva	Usaglašeno <a href="#">EU RoHS Deklaracija</a>
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	<a href="#">RoHS Deklaracija Za Kinu</a>
Informacije o RoHS izuzecima	<a href="#">Da</a>
Izjava o zaštiti okoliša	<a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.