



Main

| | |
|---------------------------|---|
| Range | Affle Plus |
| Product or component type | Switch |
| Device application | Control switch |
| Load type | Resistive Inductive Fluorescent lamp Incandescent lamp |
| Colour tint | White |

Complementary

| | |
|-------------------------|---|
| Device mounting | Flush |
| Switch function | 2-way |
| Cable cross section | 4 Mm ² stranded cable 2.5 Mm ² solid cable 2.5 Mm ² stranded cable 6 x 4 mm ² solid cable for AC |
| Rated current | 10 AX at 250 V AC |
| Number of gangs | 2 gangs |
| Material | Polycarbonate: grid plate Polycarbonate: base Polycarbonate: dolly Polycarbonate: surround Polycarbonate: actuator |
| Connections - terminals | Screw terminal Brass terminal |
| Embedding depth | 24.9 mm |
| Width | 86 mm |
| Height | 86 mm |
| Depth | 35.6 mm |

Environment

| | |
|---|--|
| Maximum ambient air temperature for operation | 35 °C |
| Relative humidity | 0...95 % |
| Operating altitude | 5000 m |
| Product certifications | IEC |
| Standards | BS EN 60669-1 MS IEC 60669-1 IEC 60669-1 |

Packing Units

| | |
|------------------------------|--------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 3.6 cm |
| Package 1 Width | 8.6 cm |
| Package 1 Length | 8.6 cm |
| Package 1 Weight | 91 g |
| Unit Type of Package 2 | BB1 |

| | |
|------------------------------|----------|
| Number of Units in Package 2 | 8 |
| Package 2 Height | 9.5 cm |
| Package 2 Width | 15 cm |
| Package 2 Length | 19 cm |
| Package 2 Weight | 732 g |
| Unit Type of Package 3 | CAR |
| Number of Units in Package 3 | 96 |
| Package 3 Height | 21 cm |
| Package 3 Width | 39.9 cm |
| Package 3 Length | 46.9 cm |
| Package 3 Weight | 9.279 kg |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |