


# LV847916SP

Additional SDE fault trip indication contact, MasterPact MTZ2/3, 1 changeover contact, low level 3A/240VAC, spare part



## Main

|                           |                                                                                          |
|---------------------------|------------------------------------------------------------------------------------------|
| Range                     | MasterPact                                                                               |
| Device short name         | SDE                                                                                      |
| Product or component type | Auxiliary contact                                                                        |
| Device application        | Control                                                                                  |
| Range compatibility       | Masterpact MasterPact MTZ2 circuit breaker<br>Masterpact MasterPact MTZ3 circuit breaker |

## Complementary

|                             |                                                                                                                                                                      |
|-----------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Auxiliary contacts type     | Low level                                                                                                                                                            |
| Signal contacts composition | 1 NO/NC                                                                                                                                                              |
| Breaking capacity           | 3 A DC-12 24/48 V DC<br>0.3 A DC-12 125 V DC<br>0.15 A DC-12 250 V DC<br>3 A AC-12 24/48 V AC 50/60 Hz<br>3 A AC-12 240 V AC 50/60 Hz<br>3 A AC-12 380 V AC 50/60 Hz |
| Minimum load                | 2 mA at 15 V                                                                                                                                                         |
| Provided equipment          | 1 instruction sheet                                                                                                                                                  |
| Offer type                  | Spare part                                                                                                                                                           |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 3.500 cm  |
| Package 1 Width              | 5.000 cm  |
| Package 1 Length             | 8.700 cm  |
| Package 1 Weight             | 101.000 g |
| Unit Type of Package 2       | BAG       |
| Number of Units in Package 2 | 4         |
| Package 2 Height             | 6.300 cm  |
| Package 2 Width              | 18.200 cm |
| Package 2 Length             | 27.300 cm |
| Package 2 Weight             | 772.000 g |
| Unit Type of Package 3       | S03       |
| Number of Units in Package 3 | 32        |
| Package 3 Height             | 30.000 cm |
| Package 3 Width              | 30.000 cm |
| Package 3 Length             | 40.000 cm |
| Package 3 Weight             | 6.176 kg  |

## Offer Sustainability

|                            |                                               |
|----------------------------|-----------------------------------------------|
| REACH Regulation           | <a href="#">REACH Declaration</a>             |
| REACH free of SVHC         | Yes                                           |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes                                           |
| Mercury free               | Yes                                           |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| RoHS exemption information | <a href="#">Yes</a>                           |