

Product data sheet

Characteristics

ZCKD41

limit switch head ZCKD - thermoplastic roller
lever variable length





Main

Range of product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKD
Head type	Rotary head
Product compatibility	XCKS XCKL XCKM

Associated body	ZCKSD35H29 ZCKM1H7 ZCKL1H7 ZCKS8 ZCKS9H29 ZCKSD31 ZCKS8H29 ZCKLD31H7 ZCKM6H29 ZCKS7H29 ZCKS7 ZCKLD37H7 ZCKM7H29 ZCKMD31H29 ZCKS2 ZCKM6 ZCKS2H29 ZCKM5H29 ZCKMD37H29 ZCKM9 ZCKSD39 ZCKL5 ZCKMD31 ZCKSD37H29 ZCKM8H7 ZCKMD39 ZCKSD39H29 ZCKL8H7 ZCKL1 ZCKM1 ZCKSD31H29 ZCKMD35H7 ZCKS6 ZCKMD37H7 ZCKM7H7 ZCKLD35 ZCKMD31H7 ZCKS9 ZCKL6 ZCKM8H29 ZCKLD37 ZCKM8 ZCKM7 ZCKS5H29 ZCKS1H29 ZCKL7H7 ZCKL8 ZCKS1 ZCKMD39H29 ZCKS5 ZCKMD35H29 ZCKL7 ZCKS6H29 ZCKLD31 ZCKLD39H7 ZCKL5H7 ZCKLD39 ZCKM5 ZCKMD39H7 ZCKSD37 ZCKLD35H7 ZCKMD37 ZCKM1H29 ZCKM5H7 ZCKL6H7 ZCKM9H29 ZCKSD35 ZCKM6H7 ZCKMD35
Movement of operating head	Rotary
Type of operator	Roller lever spring return thermoplastic (adjustable variable length)
Type of approach	Lateral approach, 2 directions

Complementary

Switch actuation	By 30° cam
Positive opening	Without
Head material	Plastic

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.500 cm
Package 1 Width	6.400 cm
Package 1 Length	9.900 cm
Package 1 Weight	95.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	28
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	2.907 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
RoHS exemption information	 Yes
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------