

ZCE11

Limit switch head, Limit switches XC Standard,
ZCE, metal end plunger with nitrile boot





Main

Range of product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCE
Head type	Plunger head
Product compatibility	XCKT XCMD XCKP XCKD

Associated body	ZCT25N12 ZCMD21L08U78 ZCD27 ZCMD21L2 ZCD28 ZCT27G11 ZCD35 ZCT28N12 ZCMD61C12 ZCT21N12 ZCP37 ZCP21M12 ZCP27 ZCT21P16 ZCT28P16 ZCMD69C12 ZCMD21L1 ZCMD29L5 ZCD21 ZCP28 ZCMD21M12 ZCMD25L5 ZCMD21L08R12 ZCMD37L1 ZCMD41L1 ZCT27P16 ZCD29M12 ZCMD81L1 ZCMD37L2 ZCD37 ZCMD21L5 ZCD29 ZCP25 ZCMD39L5 ZCD39 ZCMD61M12 ZCMD29L2 ZCT26G11 ZCT28G11 ZCP35 ZCMD25L2 ZCMD81L5 ZCMD29C12 ZCMD41L5 ZCMD39L2 ZCP21 ZCT25G11 ZCT26N12 ZCMD25L1 ZCP26 ZCP31 ZCP29 ZCP29M12 ZCT26P16 ZCD21M12 ZCP39 ZCD25 ZCMD37L5 ZCT25P16 ZCMD21C12 ZCMD81L2 ZCMD29L1 ZCD31 ZCT21G11 ZCT27N12 ZCMD39L1 ZCMD41L2 ZCD26
Movement of operating head	Linear
Type of operator	End plunger spring return metal (with nitrile boot)
Type of approach	Vertical approach, 1 direction

Complementary

Positive opening	With
------------------	------



Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	3.5 cm
Package 1 Length	2.0 cm
Package 1 Weight	14.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	3 cm
Package 2 Width	13 cm
Package 2 Length	18 cm
Package 2 Weight	140 g
Unit Type of Package 3	S01
Number of Units in Package 3	100
Package 3 Height	15 cm
Package 3 Width	15 cm
Package 3 Length	40 cm
Package 3 Weight	1.814 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	 Yes
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------