



## Main

Transformer type	Safety transformer
Range	Acti9
Range of Product	Acti9
Product name	Acti9 iTR
Product or Component Type	Transformer
Device short name	iTR

## Complementary

[Ue] rated operational voltage	230 V AC 50/60 Hz
Output voltage	12/24 V +/- 5 % on load 14/28 V off load
Output short-circuit protection	Built-in
Rated power in VA	63 VA
Temperature derating table	63 VA 35 °C 59.85 VA 40 °C 50.4 VA 50 °C 37.8 VA 55 °C 28.35 VA 60 °C
Mounting Mode	Fixed
Mounting Support	35 mm symmetrical DIN rail
9 mm pitches	10
Height	3.50 in (89 mm)
Width	3.54 in (90 mm)
Depth	2.36 in (60 mm)
Color	White
Auxiliary connection terminal	Tunnel type terminals 0.01 in <sup>2</sup> (4 mm <sup>2</sup> )

## Environment

Standards	IEC 61558-2-6 EN 60742 EN 61558-2-6
Product Certifications	NF
Overvoltage category	Class II with terminal shields in option
Ambient air temperature for operation	-4...131 °F (-20...55 °C)
Ambient Air Temperature for Storage	-13...176 °F (-25...80 °C)





## Ordering and shipping details

Category	US10DE200908
Discount Schedule	0DE2
GTIN	3606480097836
Returnability	No
Country of origin	DE

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.76 in (7.000 cm)
Package 1 Width	3.74 in (9.500 cm)
Package 1 Length	3.74 in (9.500 cm)
Package 1 Weight	2.94 lb(US) (1.332 kg)
Unit Type of Package 2	S02
Number of Units in Package 2	8
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	24.15 lb(US) (10.953 kg)
Unit Type of Package 3	P12
Number of Units in Package 3	64
Package 3 Height	17.72 in (45.000 cm)
Package 3 Width	31.50 in (80.000 cm)
Package 3 Length	47.24 in (120.000 cm)
Package 3 Weight	197.82 lb(US) (89.728 kg)

## Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	18 months
----------	-----------