



## Main

Accessory / separate part category	Connection accessories
Accessory / separate part type	Connecting cable
Accessory / separate part designation	Discrete I/O connecting cable
Product Compatibility	TWDDDO32TK TWDDDI32DK TWDDDI16DK TWDDDO16TK
Accessory / separate part destination	Modular base controller
Range Compatibility	Advantys Telefast ABE7 Twido

## Complementary

Cable length	1.64 ft (0.5 m)
Cable cross section	0.00 in <sup>2</sup> (0.08 mm <sup>2</sup> )
Electrical connection	1 connector HE10, 20 ways controller side 1 connector HE10, 20 ways Telefast ABE7 side
AWG Gauge	AWG 28
Width	4.92 in (125 mm)
Height	0.59 in (15 mm)
Depth	5.91 in (150 mm)
Net Weight	0.13 lb(US) (0.06 kg)

## Ordering and shipping details

Category	US10CP222375
Discount Schedule	OCP2
GTIN	3389110709896
Returnability	Yes
Country of origin	CN

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.59 in (1.500 cm)
Package 1 Width	4.92 in (12.500 cm)
Package 1 Length	5.91 in (15.000 cm)
Package 1 Weight	1.80 oz (51.000 g)
Unit Type of Package 2	S02
Number of Units in Package 2	50
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	6.62 lb(US) (3.001 kg)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	18 months
----------	-----------