

Product data sheet

Characteristics

SQR22102WHZ

Dimmer, X Series, Z-wave Plus energy monitoring, 600W, single pole, 3 way, matte finish, white



Main

Range	Square D X Series
Product or Component Type	Connected dimmer
Device Application	Control
Device presentation	Mechanism with fixing frame
Aesthetic name	X Series
Concentrator compatibility	Wiser hub generation 1
Mobile App name	Wiser Home
Actuator	Rocker
Colour tint	white

Complementary

Number of gangs	1 gang
Number of poles	1
Number of way	3
[Ie] rated operational current AC	5 A
[Ue] rated operational voltage	120 V
Network type	AC
Load type	Halogen 0...600 W Incandescent 0...600 W Dimmable LED 0...150 W
Mounting Mode	By screws
Device mounting	Flush
Material	Plastic: strap Metal: fixing frame
Surface Finish	Matte
Communication network type	Wireless Zigbee 2.4 GHz), 2.5 mW < 50 m
Connections - terminals	Phase and neutral 4 screw terminal copper Earth 1 screw terminal copper
Quantity per Set	1 piece

Ordering and shipping details

Category	US10DE909930
Discount Schedule	0DE9
GTIN	785901907442
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.17 in (10.6 cm)
Package 1 Width	2.13 in (5.4 cm)
Package 1 Length	2.17 in (5.5 cm)
Package 1 Weight	6.40 oz (181.5 g)
Unit Type of Package 2	CAR

Number of Units in Package 2	10
Package 2 Height	4.45 in (11.3 cm)
Package 2 Width	4.61 in (11.7 cm)
Package 2 Length	11.02 in (28.0 cm)
Package 2 Weight	3.87 lb(US) (1.754 kg)
Unit Type of Package 3	PAL
Number of Units in Package 3	1920
Package 3 Height	47.24 in (120.0 cm)
Package 3 Width	39.37 in (100.0 cm)
Package 3 Length	47.24 in (120.0 cm)
Package 3 Weight	881.34 lb(US) (399.77 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: carbon black, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes