

HMIEELCZLSPMZZ

Basic buildtime license, EcoStruxure Operator Terminal Expert, Printed



Main

Range of Product	EcoStruxure operator terminal Expert Harmony ST6
Product or Component Type	License
Format	Paper
Variant	Buildtime
Type of License	Single (1 seat)
Software Version	V3.1 to V3.X
Operating system requirement	Windows 7 64 bit Windows 8.1 64 bit Windows 10 64 bit
Processor name	Intel Core i5 4th generation Intel Core i3 8th generation 8109U
Graphics card	Intel HD Graphics, 1 GB
User Language	Spanish Portuguese Italian French English Chinese German

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Complementary

System requirements	4 GB RAM 30 GB hard-drive space
Communication port protocol	A series Ethernet CANopen slave CS/CJ series Ethernet CS/CJ series HOST link CS/CJ/NJ series Ethernet/IP DF1 DH485 Ethernet Modbus TCP/IP Ethernet TCP/IP EtherNet/IP Ethernet/Modbus TCP FX series CPU direct FX series Ethernet FX series computer link HTTP MELSEC MPI Modbus SIO master Modbus SIO slave Modbus TCP master Modbus TCP slave PacDrive Profibus DP slave Q CPU (SIO) Q series CPU direct Q series QnU CPU Ethernet Q/QnA Series Ethernet Q/QnA series serial QnA CPU (SIO) ROC Plus Ethernet ROC Plus SIO Simatic S7 Ethernet Simatic S7 MPI direct SoMachine network TIA portal Ethernet Zelio Logic IQ-R/F series Ethernet
Previous software version	V3.0
Software Designation	EcoStruxure Operator Terminal Expert
Software Function	Basic screen design and function Security feature Alarm feature Sampling and trending feature Blocky function Web viewer (additional runtime license)

Ordering and shipping details

Category	22569-MAGELIS XBT-GT (AND XBT-G)
Discount Schedule	MC2
GTIN	3606480939747
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.16 in (0.4 cm)
Package 1 Width	6.89 in (17.5 cm)
Package 1 Length	9.84 in (25.0 cm)
Package 1 Weight	1.94 oz (55.0 g)
Unit Type of Package 2	S02
Number of Units in Package 2	8
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)

Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	24.69 oz (700.0 g)
