


# LA9G3651

Mounting base, for TeSys Giga electronic  
overload relay LR9G500, independent  
mounting below contactor LC1G265-500



## Main

Range	TeSys
Device short name	LA9G
Product or Component Type	Mounting base
Accessory / separate part category	Installation accessories
Range compatibility	TeSys G LC1G contactor
Product Compatibility	LC1G265...330 LC1G300...475 LR9G500
Quantity per Set	Set of 1

## Complementary

[Ie] rated operational current	330 A
IP degree of protection	IP20 conforming to IEC 60529
Height	0.39 in (10 mm)
Width	3.74 in (95 mm)
Depth	5.71 in (145 mm)
Thickness	0.24 in (6 mm)
Net Weight	0.88 lb(US) (0.4 kg)

## Environment

Operating altitude	9842.52 ft (3000 m) without derating 5000 m with derating factor
Standards	EN/IEC 60947-4-1 UL 60947-4-1 CSA C22.2 No 60947-4-1
Pollution degree	3 IEC 60947-1
Ambient air temperature for operation	-40...140 °F (-40...60 °C)
Ambient Air Temperature for Storage	-76...176 °F (-60...80 °C)

## Ordering and shipping details

Category	US10I1222328
Discount Schedule	0I12
GTIN	3606481916563
Returnability	Yes
Country of origin	CN

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.79 in (2.0 cm)
Package 1 Width	7.09 in (18.0 cm)
Package 1 Length	7.87 in (20.0 cm)
Package 1 Weight	8.43 oz (239.0 g)

Unit Type of Package 2	S02
Number of Units in Package 2	15
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	8.86 lb(US) (4.021 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel (Metallic), which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
PVC free	Yes
Halogen content performance	Halogen free plastic parts product