



Main

Product Range	Harmony Electromechanical Relays
Product Type	Socket
Product Compatibility	relay 792XDX[RETURN] relay 782XDXH[RETURN] diode 70-BSMD[RETURN] signalling device 70-BSMLG[RETURN] suppressor module 70-BSMM[RETURN] jumper wire 16-782CBJ-1
Number of Terminals	14
Switch Function	4PDT
Contact Composition	4 C/O

Complementary

Rated Current	10 A
[Ue] rated operational voltage	300 V
Contact Terminal Arrangement	Separate
Connections Terminals	Panel lift terminals, clamping connection capacity:2 x 1.5...1 x 2.5 mm ² , AWG 16...AWG 14 flexible with cable end Panel lift terminals, clamping connection capacity:2 x 1.5...1 x 2.5 mm ² , AWG 16...AWG 14 solid with cable end
Tightening Torque	: 0.8 N.m, AWG 16...AWG 14, copper Screw: 0.8 N.m
Fixing Mode	By screw, M3, for panel Clip-on, for 35 mm symmetrical DIN rail
Shape of Screw Head	Combination roundhead
Product Weight	56 g
Width	26.9 mm
Depth	79 mm

Environment

Ambient Air Temperature for Storage	-40...105 °C
Ambient Air Temperature for Operation	-40...70 °C
IP Degree of Protection	IP20
Flame Retardance	UL94-V0
Product Certifications	UL[RETURN]CSA[RETURN]CE

Packing Units


Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.9 cm
Package 1 Width	2.69 cm
Package 1 Length	7.9 cm
Package 1 Weight	56 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	7.25 cm
Package 2 Width	9 cm

Package 2 Length	13.75 cm
Package 2 Weight	560 g
Unit Type of Package 3	CAR
Number of Units in Package 3	200
Package 3 Height	18 cm
Package 3 Width	30 cm
Package 3 Length	47 cm
Package 3 Weight	11.2 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions



(1) : Metal hold-down clip