

LAD7B106

TeSys D, separate mount kit, for LRD01 to LRD35 and LR3D01 to LR3D35 overload relays, ring tongue connectors



Main

| | |
|------------------------------------|----------------------------|
| Range | TeSys |
| Product or Component Type | Terminal block |
| Device short name | LAD |
| Product Compatibility | LRD01...35 LR3D01...D35 |
| Quantity per Set | Set of 10 |
| Accessory / separate part category | Connection accessory |

Complementary

| | |
|-------------------------|-------------------------|
| Connections - Terminals | Screw terminals for lug |
| Height | 3.35 in (85 mm) |
| Width | 1.77 in (45 mm) |
| Depth | 3.15 in (80 mm) |
| Net Weight | 0.22 lb(US) (0.1 kg) |

Ordering and shipping details

| | |
|-------------------|---------------|
| Category | US10I1222341 |
| Discount Schedule | 0I12 |
| GTIN | 3389110603521 |
| Returnability | Yes |
| Country of origin | FR |

Packing Units

| | |
|------------------------------|---------------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 1.89 in (4.800 cm) |
| Package 1 Width | 3.54 in (9.000 cm) |
| Package 1 Length | 2.95 in (7.500 cm) |
| Package 1 Weight | 3.32 oz (94.000 g) |
| Unit Type of Package 2 | S02 |
| Number of Units in Package 2 | 25 |
| Package 2 Height | 5.91 in (15.000 cm) |
| Package 2 Width | 11.81 in (30.000 cm) |
| Package 2 Length | 15.75 in (40.000 cm) |
| Package 2 Weight | 5.93 lb(US) (2.690 kg) |
| Unit Type of Package 3 | P06 |
| Number of Units in Package 3 | 400 |
| Package 3 Height | 29.53 in (75.000 cm) |
| Package 3 Width | 23.62 in (60.000 cm) |
| Package 3 Length | 31.50 in (80.000 cm) |
| Package 3 Weight | 134.26 lb(US) (60.900 kg) |

Offer Sustainability

| | |
|----------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|