



Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	60 A
Voltage Rating	120/240 V AC 240 V AC 120 V AC
Mounting Type	Bolt-on
Number of Poles	3P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs

Complementary

Interrupt Rating	22 KA 120/240 V AC 50/60 Hz 22 KA 240 V AC 50/60 Hz 22 kA 120 V AC 50/60 Hz
Number of Panel Spaces	3
Wire Size	AWG 8...AWG 2 copper or aluminium
Tightening Torque	40.71 lbf.in (4.6 N.m)
Height	3.11 in (79 mm)
Width	2.24 in (57 mm)
Depth	2.91 in (74 mm)
Net Weight	1.10 lb(US) (0.499 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00015-QOB CIRCUIT BREAKERS
Discount Schedule	DE2
GTIN	785901054832
Nbr. of units in pkg.	1
Package weight(Lbs)	17.60 oz (498.952 g)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.30 in (8.382 cm)
Package 1 width	3.90 in (9.906 cm)
Package 1 Length	2.40 in (6.096 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	33
Package 2 Weight	36.65 lb(US) (16.624 kg)
Package 2 Height	4.00 in (10.16 cm)

Package 2 width	14.00 in (35.56 cm)
Package 2 Length	20.60 in (52.324 cm)
Unit Type of Package 3	PAL
Number of Units in Package 3	1584
Package 3 Weight	1679.04 lb(US) (761.599 kg)
Package 3 Height	40.00 in (101.6 cm)
Package 3 width	40.00 in (101.6 cm)
Package 3 Length	48.00 in (121.92 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Cadmium and cadmium compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------