

Main

Product Range	Harmony Electromechanical Relays
Product Type	Socket
Product Compatibility	Relay 792XDX Relay 782XDXH
Number of Terminals	14
Switch Function	4PDT
Contact Composition	4 C/O

Complementary

Rated Current	5 A
[Ue] rated operational voltage	120 V
Contact Terminal Arrangement	Mixed
Connections Terminals	Chassis solder terminal, clamping connection capacity:0.82 mm ² , AWG 18 solid for output Chassis solder terminal, clamping connection capacity:0.82 mm ² , AWG 18 stranded for output
Tightening Torque	Chassis: 1 N.m, AWG 18, copper
Fixing Mode	By screw, M3.5, for chassis
Product Weight	6.2 g
Width	21.8 mm
Depth	57 mm

Environment

Ambient Air Temperature for Storage	-40...105 °C
Ambient Air Temperature for Operation	-40...55 °C
Flame Retardance	UL94-V0
Product Certifications	UL[RETURN]CSA[RETURN]CE

Packing Units


Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.85 cm
Package 1 Width	2.18 cm
Package 1 Length	2.062 cm
Package 1 Weight	6.2 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	2.7 cm
Package 2 Width	3.2 cm
Package 2 Length	15 cm
Package 2 Weight	62.1 g
Unit Type of Package 3	CAR
Number of Units in Package 3	1000
Package 3 Height	21 cm

Package 3 Width	29 cm
Package 3 Length	33 cm
Package 3 Weight	6.22 kg

Offer Sustainability


REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions



- (1) : Metal hold-down clip
- (2) : Recommended chassis cutout top view

Wiring Diagram



- (1) : N.C.
- (2) : N.O.
- (3) : COM
- (4) : Input
- (5) : Ground lug