



### Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G duct
Installation description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm
Mounting plate description	Recessed slotted
Number of vertical modules [50 mm]	6 module(s) in 300 mm Widefloor-standing duct 6 module(s) in 300 mm Widewall-mounted duct
Standards	IEC 61439-2
Product certifications	ASTA

### Complementary

Material	Steel
Surface finish	Galvanized
Width	300 mm
Height	300 mm
Net weight	0.44 kg
Functional unit	300 mm PrismaSeT G floor-standing duct 6 12.5 mm 300 mm PrismaSeT G wall-mounted duct 6 12.5 mm

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.000 cm
Package 1 Width	21.500 cm
Package 1 Length	30.000 cm
Package 1 Weight	460.000 g
Unit Type of Package 2	S02
Number of Units in Package 2	5
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	2.500 kg
Unit Type of Package 3	P12
Number of Units in Package 3	40
Package 3 Height	30.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	32.000 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product