



Main

Range	PrismaSeT
Range of product	PrismaSeT G PrismaSeT P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G duct PrismaSeT PrismaSeT P cubicle
Type of front plate	Cut-out
Installed device	ComPact: fixed NSX400 with earth leakage protection - control: toggle - vertical installation ComPact: plug-in NSX400 with earth leakage protection - control: toggle - vertical installation ComPact: fixed NSX630 with earth leakage protection - control: toggle - vertical installation ComPact: plug-in NSX630 with earth leakage protection - control: toggle - vertical installation
Poles description	1 x 4P: mounting plate support: NSX400 vertical installation 1 x 3P: mounting plate support: NSX400 vertical installation 1 x 3P: mounting plate support: NSX630 vertical installation 1 x 4P: mounting plate support: NSX630 vertical installation
Operating position	Vertical

Complementary

Enclosure/cubicle description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Cubicle duct - width 400 mm depth 400 mm
Connection position	Direct connection Front connection
Number of vertical modules [50 mm]	9
Standards	IEC 61439-1 IEC 61439-2
Product certifications	ASTA
Material	Steel
Surface finish	Matt Textured
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	500 mm
Width	250 mm
Net weight	1 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Quantity per set	Set of 1
Functional unit	<p>300 mm PrismaSeT G floor-standing duct ComPact NSX400 with fixed toggle vertical 4P 1 direct</p> <p>300 mm PrismaSeT G wall-mounted duct ComPact NSX400 with fixed toggle vertical 4P 1 direct</p> <p>400 mm 400 mm PrismaSeT P cubicle ComPact NSX400 with fixed toggle vertical 3P 1 front connection 14</p> <p>400 mm 400 mm PrismaSeT P cubicle ComPact NSX400 with fixed toggle vertical 4P 1 front connection 14</p> <p>400 mm 400 mm PrismaSeT P cubicle ComPact NSX400 with plug-in toggle vertical 3P 1 front connection 14</p> <p>400 mm 400 mm PrismaSeT P cubicle ComPact NSX400 with plug-in toggle vertical 4P 1 front connection 14</p> <p>400 mm 400 mm PrismaSeT P cubicle ComPact NSX630 with fixed toggle vertical 3P 1 front connection 14</p> <p>400 mm 400 mm PrismaSeT P cubicle ComPact NSX630 with fixed toggle vertical 4P 1 front connection 14</p> <p>400 mm 400 mm PrismaSeT P cubicle ComPact NSX630 with plug-in toggle vertical 3P 1 front connection 14</p> <p>400 mm 400 mm PrismaSeT P cubicle ComPact NSX630 with plug-in toggle vertical 4P 1 front connection 14</p> <p>300 mm PrismaSeT G floor-standing duct ComPact NSX400 with fixed toggle vertical 3P 1 direct with long terminal shield 14</p> <p>300 mm PrismaSeT G wall-mounted duct ComPact NSX400 with fixed toggle vertical 3P 1 direct with long terminal shield 14</p> <p>300 mm PrismaSeT G floor-standing duct ComPact NSX400 with fixed toggle vertical 4P 1 direct with long terminal shield 14</p> <p>300 mm PrismaSeT G wall-mounted duct ComPact NSX400 with fixed toggle vertical 4P 1 direct with long terminal shield 14</p> <p>300 mm PrismaSeT G floor-standing duct ComPact NSX630 with fixed toggle vertical 3P 1 direct with long terminal shield 14</p> <p>300 mm PrismaSeT G wall-mounted duct ComPact NSX630 with fixed toggle vertical 3P 1 direct with long terminal shield 14</p> <p>300 mm PrismaSeT G floor-standing duct ComPact NSX630 with fixed toggle vertical 4P 1 direct with long terminal shield 14</p> <p>300 mm PrismaSeT G wall-mounted duct ComPact NSX630 with fixed toggle vertical 4P 1 direct with long terminal shield 14</p>

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	26.5 cm
Package 1 Length	51.5 cm
Package 1 Weight	996.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	17.0 cm
Package 2 Width	27.5 cm
Package 2 Length	52.5 cm
Package 2 Weight	10.205 kg
Unit Type of Package 3	P12
Number of Units in Package 3	270
Package 3 Height	95.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	286.5 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product