

# LVS03410

## Mounting Plate, PrismaSeT P, for 5/4 NSXm Toggle/Rotative 3P/4P Vertical fixed, enclosure W650mm



### Main

Range	PrismaSeT
Range of product	PrismaSeT P
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT P cubicle ComPact ComPact NSXm circuit breaker
Installation description	Cubicle - width 650 mm depth 400 mm
Mounting plate description	Dedicated
Installed device	ComPact: fixed NSXm without earth leakage protection - control: toggle - vertical installation ComPact: fixed NSXm without earth leakage protection - control: direct rotary handle - vertical installation
Poles description	5 x 3P: fixed NSXm vertical installation 4 x 4P: fixed NSXm vertical installation
Number of vertical modules [50 mm]	8 module(s): NSXm without earth leakage protection , direct
Standards	IEC 61439-2
Product certifications	ASTA

### Complementary

Material	Sheet steel
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Matt Textured
Colour	White (RAL 9003)
Width	575 mm
Height	150 mm
Functional unit	650 mm 400 mm PrismaSeT P cubicle ComPact NSXm without fixed toggle vertical 3P 5 direct 8 162.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSXm without fixed toggle vertical 4P 4 direct 8 162.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSXm without fixed direct rotary handle vertical 3P 5 direct 8 162.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSXm without fixed direct rotary handle vertical 4P 4 direct 8 162.5 mm

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	14.5 cm
Package 1 Length	58.0 cm
Package 1 Weight	2.547 kg
Unit Type of Package 2	S04
Number of Units in Package 2	6

Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	16.021 kg
Unit Type of Package 3	P12
Number of Units in Package 3	72
Package 3 Height	102.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	205.5 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product