

Main

Range	PrismaSeT
Range of product	PrismaSeT P
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT P cubicle
Installation description	Cubicle - width 650 + 150 mm depth 400 mm
Installed device	ComPact: fixed INV800...1250 + NS800...1250 without earth leakage protection - control: toggle - vertical installation
Poles description	1 x 3P: fixed INV800...1250 + NS800...1250 vertical installation 1 x 4P: fixed INV800...1250 + NS800...1250 vertical installation
Standards	IEC 61439-2 NF C 15-100

Complementary







Material	Sheet steel
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Matt Textured
Colour	White (RAL 9003)
Width	575 mm
Height	500 mm
Net weight	5.26 kg
Functional unit	650 + 150 mm 400 mm PrismaSeT P cubicle ComPact INV800...1250 + NS800...1250 without fixed toggle vertical 3P 1 262.5 mm 650 + 150 mm 400 mm PrismaSeT P cubicle ComPact INV800...1250 + NS800...1250 without fixed toggle vertical 4P 1 262.5 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	50 cm
Package 1 Length	58 cm
Package 1 Weight	5.24 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	2
Package 2 Height	15 cm
Package 2 Width	53.5 cm
Package 2 Length	81.5 cm
Package 2 Weight	11.53 kg
Unit Type of Package 3	P12
Number of Units in Package 3	24
Package 3 Height	114 cm
Package 3 Width	80 cm

Package 3 Length	120 cm
Package 3 Weight	166.53 kg

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
BVB	 Accepted
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product
Take-back	No