



## Main

Range	PrismaSeT
Range of product	PrismaSeT P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT P cubicle
Type of front plate	Cut-out
Installed device	ComPact: fixed INS320...630 source changeover - control: direct front rotary handle - horizontal installation
Poles description	2 x 3P: mounting plate support: INS320...630 source changeover horizontal installation 2 x 4P: mounting plate support: INS320...630 source changeover horizontal installation
Operating position	Horizontal

## Complementary

Enclosure/cubicle description	Cubicle - width 650 mm depth 400 mm
Connection position	Direct connection
Number of vertical modules [50 mm]	10
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASTA
Material	Steel
Surface finish	Textured Matt
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	500 mm
Width	500 mm
Net weight	1.54 kg
Quantity per set	Set of 1
Functional unit	650 mm 400 mm PrismaSeT P cubicle ComPact INS320...630 source changeover fixed direct front rotary handle horizontal 3P 2 direct 10 650 mm 400 mm PrismaSeT P cubicle ComPact INS320...630 source changeover fixed direct front rotary handle horizontal 4P 2 direct 10

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	51 cm
Package 1 Length	51.5 cm
Package 1 Weight	1.703 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	6
Package 2 Height	11 cm

Package 2 Width	52.5 cm
Package 2 Length	53 cm
Package 2 Weight	10.684 kg
Unit Type of Package 3	P12
Number of Units in Package 3	36
Package 3 Height	46 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	75 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product